

## Sealants and Packing Material

### 3M™ Fire Barrier Sealant IC 15WB+

3M™ Fire Barrier Sealant IC 15WB+ is an economical, one-part, gun-grade, latex-based, intumescent firestop sealant that dries to form a monolithic firestop seal that also acts as a barrier to airborne sound transmission. 3M Fire Barrier Sealant IC 15WB+ firestops through penetrations passing through fire-rated floor, floor/ceiling or wall assemblies, as well as other fire-rated interior building partitions and assemblies (e.g. static construction joints or blank openings). In addition, the unique intumescent property of this material allows 3M Fire Barrier Sealant IC 15WB+ to expand and help maintain a firestop penetration seal for up to 3 hours as penetrants are exposed to fire. 3M Fire Barrier Sealant IC 15WB+ bonds to most construction substrates, including: gypsum wallboard, concrete, metals, wood, plastic (including CPVC) and cable jacketing. No mixing is required.

<b>Description</b>	Intumescent Sealant
<b>Properties</b>	Latex Based
<b>Application Temperature Range</b>	40–122°F (4–50°C)
<b>RoHS 2011/65/EU</b>	Undetermined
<b>Specifications</b>	Fire Barrier up to 3 Hr; Smoke Seal L Rated; STC Rating 54; L-Rating; LEED® VOC environmental requirements
<b>Agency Approvals</b>	IBC; IRC, NBCC; IFC; IPC; IMC; NPFA 5000; NEC (NFPA 70); NFPA 101



Order No.	UPC	Product Name	Color	Size	Min. Order Qty.	Case Quantity
IC-15WB+-10.1OZ	051115-16557	3M™ Fire Barrier Sealant IC 15WB+, 10.1 fl. oz., Cartridge	Yellow	10.1 fl oz (296 ml)	12	12
IC-15WB+-20OZ	051115-16560	3M™ Fire Barrier Sealant IC 15WB+, 20 fl. oz., Sausage	Yellow	20 fl oz (591 ml)	10	10
IC-15WB+-4.5GAL	051115-16558	3M™ Fire Barrier Sealant IC 15WB+, 4.5 gallon, Pail	Yellow	4.5 gal (15,1 l)	1	1

### 3M™ Fire Block Sealant FB 136

3M™ Fire Block Sealant FB 136 is a one component, non-combustible draft, smoke and fireblocking sealant, designed to resist high temperatures and smoke passage in non-rated construction. Fire Block Sealant FB 136 meets ASTM E-136, current 2003 International Building Code (IBC), 2003 International Residential Code (IRC), 2003 International Residential Mechanical Code, 2003 International Fuel Gas Code and NFPA 5000 draft, smoke and fireblocking requirements.

3M™ Fire Block Sealant FB 136 features excellent adhesion strength, caulk rate and no sag application.

3M™ Fire Block Sealant FB 136 can be installed with a standard caulking gun, pneumatic pumping equipment or it can be easily applied with a putty knife or trowel. Fire Block Sealant FB 136 will bond to concrete, brick, metals, wood, plastic and cable jacketing. No mixing is required.

<b>Description</b>	Water Based Sealant
<b>Agency Approvals</b>	IBC; IFC; IRC; International Residential Mechanical Code; International Fuel Gas Code; NFPA 5000



Order No.	UPC	Product Name	Color	Size	Min. Order Qty.	Case Quantity
FB-136	051115-16591	3M™ Fire Block Sealant FB 136, 10.1 fl. oz., Cartridge	Gray	10.1 fl oz (298 ml)	12	12