


## AMT Connectors



### AMT Connectors



The high quality and built-in flexibility of the new Blackburn® AMT Connectors reduce the cost of field installations on splices, taps, and terminations. They're easy and quick to install, and provide superior insulation that lasts the life of the connection.

#### Features and Benefits:

- PVC insulation eliminates insulation failures and reduces outage costs
- UV resistant material
- Compact design provides space efficiencies
- UL Listed.

Cat. No.	Description	Fig.	UPC	Std. Ctn.
AMTD50066	Insulated Six Hole Both Sides For 500-#6 AWG	5	783786-25947	10
AMTD50065	Insulated Five Hole Both Sides For 500-#6 AWG	5	783786-25946	10
AMTD50064	Insulated Four Hole Both Sides For 500-#6 AWG	5	783786-25945	10
AMTD50063	Insulated Three Hole Both Sides For 500-#6 AWG	5	783786-25944	10
AMT500	Insulated Two Hole Same Side For 500-#6 AWG	2	783786-25925	25
AMTD350106	Insulated Six Hole Both Sides For 350-#10 AWG	5	783786-25943	10
AMTD350105	Insulated Five Hole Both Sides For 350-#10 AWG	5	783786-25942	10
AMTD350104	Insulated Four Hole Both Sides For 350-#10 AWG	5	783786-25941	25
AMTD350103	Insulated Three Hole Both Sides For 350-#10 AWG	5	783786-25940	25
AMTS350106	Insulated Six Hole Same Side For 350-#10 AWG	4	783786-25937	10
AMTS350105	Insulated Five Hole Same Side For 350-#10 AWG	4	783786-25936	10
AMTS350104	Insulated Four Hole Same Side For 350-#10 AWG	4	783786-25935	25
AMTS350103	Insulated Three Hole Same Side For 350-#10 AWG	4	783786-25934	25
AMT350	Insulated Two Hole Same Side For 350-#10 AWG	2	783786-25924	25
AMTS250108	Insulated Eight Hole Same Side For 250-#10 AWG	4	783786-25933	10
AMTD250106	Insulated Six Hole Both Sides For 250-#10 AWG	5	783786-25939	10
AMTD250105	Insulated Five Hole Both Sides For 250-#10 AWG	5	783786-25938	10
AMTD250104	Insulated Four Hole Both Sides For 250-#10 AWG	5	783786-25927	25
AMTD250103	Insulated Three Hole Both Sides For 250-#10 AWG	5	783786-25926	25
AMTT250	Insulated Two Hole Opposite Sides for 250-#10 AWG	3	783786-25923	25
AMT250	Insulated Two Hole Same Side for 250-#10 AWG	2	783786-25922	25
AMTS414	Insulated Four Hole Same Side for #4-#14 AWG	4	783786-25932	25
AMTTC4	Insulated Two Hole Opposite Sides for #4-#14 AWG	3	783786-25919	25
AMTC4	Insulated Two Hole Same Side for #4-#14 AWG	2	783786-25917	25
AMTT20	Insulated Two Hole Opposite Sides for 2/0-#14 AWG	3	783786-25921	25
AMT20	Insulated Two Hole Same Side for 2/0-#14 AWG	2	783786-25920	25
AMTSR500	Insulated Aluminum Splice 500-#10 AWG	1	783786-25931	25
AMTSR350	Insulated Aluminum Splice 350-#6 AWG	1	783786-25930	25
AMTSR250	Insulated Aluminum Splice 250-#6 AWG	1	783786-25929	25
AMTSR10	Insulated Aluminum Splice 1/0-#14 AWG	1	783786-25928	25




Fig. 1




Fig. 2




Fig. 3




Fig. 4




Fig. 5