

Portable Labelers

3M™ Portable Labeler Accessories

The following accessories are available for the 3M™ Portable Labeler family: Lithium-ion Battery Packs, Hard Carrying Cases and AC Adaptors.

Manufactured by



Order No.	UPC	Product Name	Description	Compatible With	Min. Order	Case Qty.
PL-ACPS	051128-58518	3M™ Portable Labeler AC Power Supply PL-ACPS	AC Power Supply	PL200/PL300	1	60
PL150-PL200-BAT	051128-58517	3M™ Portable Labeler Rechargeable Battery Pack PL150-PL200-BAT	Rechargeable Battery Pack	PL150, PL200	1	48
PL150 SOFT CASE	051128-60252	3M™ Portable Labeler Soft Case PL150 SOFT CASE	Soft Case	PL150	1	3
PL200-HARD CASE	051128-58515	3M™ Portable Labeler Hard Case PL200-HARD CASE	Hard Case	PL200	1	3
PL300-BAT	051128-58520	3M™ Portable Labeler Rechargeable Battery Pack PL300-BAT	Rechargeable Battery Pack	PL300	1	60
PL300 HARD CASE	051128-59108	3M™ Portable Labeler Hard Case PL300-HARD CASE	Hard Case	PL300	1	3
PL300 SOFTWARE	051128-59363	3M™ Portable Labeler Software CD	PL300 Software	PL300	1	50

3M™ Portable Labeler Refill Cartridges

3M™ Portable Labeler Refill Cartridges are available in a variety of materials, including heat shrink, for a variety of surfaces and environments. The label cartridges are interchangeable, easy to install and remove, and have less waste.

Manufactured by



Order No.	UPC	Material	Width	Length	Color (Font)	Color (Label)	Compatible With	Min. Order	Case Qty.
PLFN-YEL-1	051128-58514	Flexible Nylon	1" (24 mm)	11.5'	Black	Yellow	PL300	5	25
PLFN-YEL-3/4	051128-58513	Flexible Nylon	3/4" (19 mm)	11.5'	Black	Yellow	PL150, PL200, PL300	5	25
PLFN-YEL-1/2	051128-58512	Flexible Nylon	1/2" (12 mm)	11.5'	Black	Yellow	PL100, PL150, PL200, PL300	5	25
PLFN-WHT-1	051128-58511	Flexible Nylon	1" (24 mm)	11.5'	Black	White	PL300	5	25
PLFN-WHT-3/4	051128-58510	Flexible Nylon	3/4" (19 mm)	11.5'	Black	White	PL150, PL200, PL300	5	25
PLFN-WHT-1/2	051128-58509	Flexible Nylon	1/2" (12 mm)	11.5'	Black	White	PL100, PL150, PL200, PL300	5	25
PLHS-YEL-1/4	051128-58484	Heat Shrink	1/4" (6 mm)	5.0'	Black	Yellow	PL150, PL200, PL300	5	25
PLHS-WHT-1/4	051128-58483	Heat Shrink	1/4" (6 mm)	5.0'	Black	White	PL150, PL200, PL300	5	25

Portable Labelers

3M™ Portable Labeler Refill Cartridges (continued)

Order No.	UPC	Material	Width	Length	Color (Font)	Color (Label)	Compatible With	Min. Order	Case Qty.
PLV-ORG-3/4	051128-58469	Vinyl	3/4" (19 mm)	18.0'	Black	Orange	PL150, PL200, PL300	5	25
PLV-ORG-1/2	051128-58468	Vinyl	1/2" (12 mm)	18.0'	Black	Orange	PL100, PL150, PL200, PL300	5	25
PLV-YEL-3/4	051128-58463	Vinyl	3/4" (19 mm)	18.0'	Black	Yellow	PL150, PL200, PL300	5	25
PLV-YEL-1/2	051128-58462	Vinyl	1/2" (12 mm)	18.0'	Black	Yellow	PL100, PL150, PL200, PL300	5	25
PLV-WHT-3/4	051128-58460	Vinyl	3/4" (19 mm)	18.0'	Black	White	PL150, PL200, PL300	5	25
PLV-WHT-1/2	051128-58459	Vinyl	1/2" (12 mm)	18.0'	Black	White	PL100, PL150, PL200, PL300	5	25
PLV-WHT-3/8	051128-58458	Vinyl	3/8" (9 mm)	18.0'	Black	White	PL100, PL150, PL200, PL300	5	25

3M™ Portable Labeler Embosser PLE

The 3M™ Portable Labeler Embosser PLE is tough enough to accompany you in the field and is easy-to-use. Since it can make labels on site that are capable of weathering harsh conditions, there's no need for time-consuming trips to an engraving shop. All you'll have to do is type, cut and apply.

Front Scissor Cut-Off Yes
 Built-In Hole Punching Device Yes
 Manufactured by

DYMO



Order No.	UPC	Description/Kit Contents	Imprint Size	Length	Product Type	Min. Order	Case Qty.
PLE	051128-59109	(1) 3M™ Portable Labeler Embosser PLE – Metal Tape; (1) Reverse image wheel; (1) Roll 1/2" (12 mm) x 12' (4,8 m); (1) Roll 1/2" (12 mm) x 21' (6,40 m); (1) Carrying case; (1) Instruction manual	1/2" (12 mm) wide metal tapes	–	Embosser	1	3
PLE-ALA-1/2	051128-59107	Aluminum tape for 3M™ Portable Labeler Embosser PLE. 1/2" (12 mm) Aluminum with adhesive.	–	12'	Tape	10	100
PLE-ALNA-1/2	051128-59105	Aluminum tape for 3M™ Portable Labeler Embosser PLE. 1/2" (12 mm) Aluminum with no adhesive.	–	16'	Tape	10	100
PLE-SSNA-1/2	051128-59106	Stainless steel tape for 3M™ Portable Labeler Embosser PLE. 1/2" (12 mm) Stainless steel tape with no adhesive.	–	21'	Tape	10	100