



ULTIMATE PRODUCTIVITY

Quick and Accurate Die Selection with the SYNCRO Crimpers

NEW

K-SERIES CRIMPING TOOL

K09-SYNCRO

**Produce accurate uniform crimps
faster and with less force**

Productive

- Built-in dies eliminate loose pieces and speed up crimping process
- Patented SYNCRO die design – one dial rotates both dies, preventing die misalignment and reducing rework
- Color-coded one dial die selection wheel for quick and easy die selection
- Engraved crimp groove allows for easy verification that the connection was made properly

Ergonomic

- Locking, extendable handles with four length positions provide increased maneuverability and leverage
- Handle design and grips effectively transmit arm force to the tool, making it easier and more comfortable to use
- Up to 35% less muscle effort than the competition

Durable

- Continues to accurately crimp after 10,000 cycles
- Phosphated, polished, and tempered dies for increased durability and corrosion resistance

ULTIMATE PRODUCTIVITY

K-SERIES CRIMPING TOOL

K09-SYNCRO



Color-Coded Die Selection Wheel
Quick and easy die selection increases operator efficiency



Locking Extendable Handles
Improve maneuverability and leverage



Ergonomic Molded Grips
Improved comfortable grip



SYNCRO Die Design
One-handed die change rotates both dies simultaneously and prevents misalignment of dies



Versatility
UL and cUL Classified to seven major brands of lugs and connectors*



K09-SYNCRO



K05-SYNCRO



CLASSIFIED
cUL US
95R7

THE SYNCRO CRIMPER FAMILY

K05-SYNCRO SPECIFICATIONS

CAPACITY:	8 TO 1/0 AWG
LENGTH:	16"
WEIGHT:	2.6 lbs (1.18 kg)

K09-SYNCRO SPECIFICATIONS

CAPACITY:	1 AWG TO 250 kcmil
LENGTH:	23.62" – 29.52"
WEIGHT:	5.7 lbs (2.6 kg)

ORDERING INFORMATION

CAT. NO.	UPC NO.	DESCRIPTION
K05-SYNCRO	06440	Crimping Tool (8 AWG – 1/0 AWG)
K09-SYNCRO	06441	Crimper (1 AWG – 250 kcmil)

*UL and cUL classified with Anderson®, Blackburn®, Burndy®, ILSCO®, Panduit®, Thomas & Betts® and Penn-Union® copper connectors.

Anderson® and Brundy® are registered trademarks of Hubbell Incorporated. Blackburn® and Thomas & Betts® are registered trademarks of Thomas & Betts International, Inc. ILSCO® is a registered trademark of ILSCO Corporation. Panduit® is a registered trademark of Panduit Corp. Penn-Union® is a registered trademark of Penn Union Corp.