



PL-T Triple 4-Pin Base

PL-T 26W/830/A/4P/ALTO

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum effciency and sleek design solutions are required.

Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information				
Base	GX24Q-3 [GX24q-3]			
LSF Preheat 2000 h Rated	99 %			
LSF Preheat 4000 h Rated	98 %			
LSF Preheat 6000 h Rated	97 %			
LSF Preheat 8000 h Rated	90 %			
Light Technical				
Color Code	830 [CCT of 3000K]			
Initial lumen (Nom)	1750 lm			
Luminous Flux (Rated) (Nom)	1750 lm			
Color Designation	Warm White (WW)			
Correlated Color Temperature (Nom)	3000 K			
Luminous Efficacy (rated) (Nom)	64.8 lm/W			
Color Rendering Index (Nom)	>80			
LLMF 2000 h Rated	92 %			


LLMF 4000 h Rated	88 %	
LLMF 6000 h Rated	85 %	
LLMF 8000 h Rated	84 %	
LLMF 12000 h Rated	81 %	
Operating and Electrical		
Power (Rated) (Nom)	26 W	
Lamp Current (Nom)	0.335 A	
Temperature		
Design Temperature (Nom)	28 ℃	
Controls and Dimming		
Dimmable	Yes	

PL-T Triple 4-Pin Base

Mechanical and Housing	
Cap-Base Information	4P
Approval and Application	
Energy Efficiency Label (EEL)	В
Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	PL-T 26W/830/A/4P/ALTO

EAN/UPC - Product	046677268237		
Order code	458257		
Numerator - Quantity Per Pack	1		
Numerator - Packs per outer box	10		
Material Nr. (12NC)	927910983050		
Net Weight (Piece)	64.000 g		
ILCOS Code	FSM-26/30/1B-E-GX24q=3		


Dimensional drawing



Product	D (max)	A (max)	B (max)	C (max)
PL-T 26W/830/A/4P/ALTO	41 mm	86.7 mm	111.0 mm	126.7 mm

Photometric data

Φ = - - -




LDPB_PLTTOP4P_830-Spectral power distribution B/W


LDPO_PLTTOP4P_830-Spectral power distribution Colour

PL-T Triple 4-Pin Base

Lifetime



LDLM_PLTTOP4P_0001-Lumen maintenance diagram



LDLE_PLTTOP4P_0002-Life expectancy diagram



© 2021 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

LDLE_PLTTOP4P_0001-Life expectancy diagram