

3-OUTLET OUTDOOR CORDS

Part No.	Cord Length	Gauge/Conductor	Wire Type	Colour
545502	10 metre	16/3	SJTW	Orange
545528	15 metre	16/3	SJTW	Orange
545609	10 metre	14/3	SJTW	Red



POLAR WINTERFLEX™ 3-OUTLET POWER CORDS

•Tested to stay flexible even in -50°C •Female outlets won't constrict, making it easy to plug and unplug male ends after prolonged exposure to extreme cold •Resistant to oil and fuel

Part No.	Cord Length	Gauge/Conductor	Wire Type	Colour
3-Outlet				
545781	10 metre	16/3	SJOW	Black
545782	15 metre	16/3	SJOW	Black
3-Outlet with Power Indicator Light				
545337	2 metre	16/3	SJOW	Black
545339	10 metre	16/3	SJOW	Black
545345	10 metre	14/3	SJOW	Black



COLD FLEX™ EXTREME COLD WEATHER CORDS

•ColdFlex™ jacket is meant for colder temperatures down to -50°C •Female outlets won't constrict, making it easy to plug and unplug male ends even after exposure to extreme cold •Blue male and female ends

Part No.	Cord Length	Gauge/Conductor	Wire Type	Colour
Single Outlet				
510663	15 metre	14/3	SJTW	Blue
510664	30 metre	14/3	SJTW	Blue
510670	30 metre	12/3	SJTW	Blue
3-Outlet				
510844	3 metre	16/3	SJTW	Blue
510845	5 metre	16/3	SJTW	Blue
510846	10 metre	16/3	SJTW	Blue
510847	15 metre	16/3	SJTW	Blue



3-OUTLET CUBE TAP CORDS

•Great for general indoor use with lamps, radios, clocks, etc. •Polarized plugs •125 volts, 13 amps

Part No.	Cord Length	Gauge/Conductor	Wire Type	Colour
540002	2 metre	16/2	SPT-2	Brown



AIR CONDITIONER CORDS

•1 outlet •Right angle plug •Also ideal for portable tools

Part No.	Cord Length	Gauge/Conductor	Wire Type	Colour
542648	4.5 metre	16/3	SPT-3	Beige



CORD CADDY

•This self-storing extension cord allows up to four tools or appliances to be plugged in either indoors or outdoors •4 grounded outlets •Overload protection with built-in 10 amp circuit breaker protects tools •Impact resistant reel •Eliminates messy, tangled extension cords – unwind only as much cord as needed, quick and easy to rewind •Safe, neat storage protects cord from damage •16/3 gauge •SJTW •10 metre cord •Orange cord
Part No. 545794.



PLUG-IN GFCI & SURGE PROTECTOR

•Use anywhere GFCI or Surge Protection is desired: job sites, kitchens, bathrooms, garages and workshops •Detects power leaks and cuts electricity off in less than a second to prevent electrical shock •Protects electrical circuitry from voltage fluctuations •Manual test-reset buttons – provides maximum safety.

Part No. 582762.

