













Project: _____

Fixture Type: _____

Location: _____

Contact/Phone: _____

Trim Series	Dimensions	Aperture	Catalog No.	Housing/ Lamp Compatibility
 Flushed Gimbal Ring	 5"		10 ABZ 4" Adjustable Flush Gimbal Ring Trim - Classic Aged Bronze 10 BL 4" Adjustable Flush Gimbal Ring Trim - Black 10 SC 4" Adjustable Flush Gimbal Ring Trim - Satin Chrome 10 WH 4" Adjustable Flush Gimbal Ring Trim - White	IC1P / TC1 / TC1 S / TC1R : 50W PAR20, 75W ES20 (Requires GU10WHIP) TC1RC W: 50W PAR20 APT1: 50W PAR20, 75W ES20 (Requires GU10WHIP)
 Mini Eyeball PAR16/ R16	 5"		18 SC 4" Adjustable Mini Eyeball Trim - Satin Chrome 18 WH 4" Adjustable Mini Eyeball Trim - White	IC1 / IC1 W/ IC1 S/ IC1P/ TC1/ TC1 S/ TC1R: 60W PAR16, 40W R16 TC1RC W: 60W PAR16 APT1: 60W PAR16, 40W R16
 Mini Eyeball R16 / R14 (Intermediate Base)	 5"		19 WH 4" Adjustable Mini Eyeball Trim - White	IC1 / IC1 W/ IC1 S/ IC1P/ TC1/ TC1 S/ TC1R: 25W R14, 40W R16 (Intermediate Screw Base) APT1: 40W R14, 40W R16 (Intermediate Screw Base)
 Flush Gimbal Ring	 5"		440 ABZ 4" Adjustable Flush Gimbal Ring Trim - Classic Aged Bronze 440 BL 4" Adjustable Flush Gimbal Ring Trim - Black 440 SC 4" Adjustable Flush Gimbal Ring Trim - Satin Chrome 440 WH 4" Adjustable Flush Gimbal Ring Trim - White	IC1 / IC1 W/ IC1 S: 35W MR16, 35W ES16 120V GU10 Base (Requires GU10WHIP) IC1P / TC1 / TC1 S/ TC1RC W: 50W MR16, 50W MR16, 50W PAR16, 50W ES16 120V GU10 Base (Requires GU10WHIP) APT1: 50W MR16, 50W PAR16, 50W ES16 GU10 (Requires GU10WHIP)
 Adjustable Slot Aperture	 5"	1-1/2" x 2-1/8" Oblong	445 WH 4" Adjustable Slot Aperture Trim - White	IC44N/IC44N W/IC44N S/TC44/TC44 V/TC44 S/TC44R: 50W MR16 TC47/TC47 V: 75W MR16 APT44: 50W MR16
 Eyeball with Black Baffle	 5"		448 SC 4" Adjustable Eyeball with Black Baffle Trim - Satin Chrome 448 WH 4" Adjustable Eyeball with Black Baffle Trim - White	IC1 / IC1 W/ IC1 S: 35W MR16, 35W ES16 120V GU10 Base (Requires GU10WHIP) IC1P: 50W MR16, 50W ES16 120V GU10 Base (Requires GU10WHIP) TC1 / TC1 S/ TC1R/ TC1RC W: 50W MR16, 50W PAR16, 50W ES16 120V GU10 Base (Requires GU10WHIP) APT1: 50W MR16, 50W PAR16, 50W ES16 GU10 (Requires GU10WHIP)

Housing and trim can be ordered together or separate, but will always ship separately.