

RED HELIX™ COBALT DRILL BITS

Diameter	Shank	Variable Helix	Chip Breaker	SKU
1/16"	Round			48-89-2301
5/64"	Round			48-89-2302
3/32"	Round			48-89-2303
7/64"	Round			48-89-2304
1/8"	Round	X		48-89-2305
9/64"	Round	X		48-89-2306
5/32"	Round			48-89-2307
11/64"	Round	X		48-89-2308
3/16"	3-Flat	X	X	48-89-2309
13/64"	3-Flat	X	X	48-89-2310
7/32"	3-Flat	X	X	48-89-2311
15/64"	3-Flat	X	X	48-89-2312
1/4"	3-Flat	X	X	48-89-2313
17/64"	3-Flat	X	X	48-89-2314
9/32"	3-Flat	X	X	48-89-2315
19/64"	3-Flat	X	X	48-89-2316
5/16"	3-Flat	X	X	48-89-2317
21/64"	3-Flat	X	X	48-89-2318
11/32"	3-Flat	X	X	48-89-2319
23/64"	3-Flat	X	X	48-89-2320
3/8"	3-Flat	X	X	48-89-2321
25/64"	3/8" Reduced 3-Flat	X	X	48-89-2322
27/64"	3/8" Reduced 3-Flat	X	X	48-89-2324
7/16"	3/8" Reduced 3-Flat	X	X	48-89-2325
29/64"	3/8" Reduced 3-Flat	X	X	48-89-2326
15/32"	3/8" Reduced 3-Flat	X	X	48-89-2327
13/32"	3/8" Reduced 3-Flat	X	X	48-89-2323
1/2"	3/8" Reduced 3-Flat	X	X	48-89-2329

RED HELIX™ COBALT DRILL BIT KIT

Description	Includes	SKU
15 Piece Cobalt RED HELIX™ Kit	(1) 1/16" COBALT RED HELIX™ Drill Bit (48-89-2301) (1) 5/64" COBALT RED HELIX™ Drill Bit (48-89-2302) (1) 3/32" COBALT RED HELIX™ Drill Bit (48-89-2303) (1) 7/64" COBALT RED HELIX™ Drill Bit (48-89-2304) (2) 1/8" COBALT RED HELIX™ Drill Bit (48-89-2305) (1) 9/64" COBALT RED HELIX™ Drill Bit (48-89-2306) (1) 5/32 Milwaukee® Thunderbolt® Cobalt Drill Bit (48-89-2307) (1) 3/16" COBALT RED HELIX™ (48-89-2309) (1) 7/32" COBALT RED HELIX™ (48-89-2311) (2) 1/4" COBALT RED HELIX™ (48-89-2313) (1) 5/16 Milwaukee® Thunderbolt® Cobalt Drill Bit (48-89-2317) (1) 3/8" COBALT RED HELIX™ (48-89-2321) (1) 1/2 Milwaukee® Thunderbolt® Cobalt Drill Bit (48-89-2329)	48-89-2331

THUNDERBOLT® TITANIUM-COATED DRILL BITS