



TRAC- LITES

Line and Low Voltage

MONOPOINTS

and SPECIAL MOUNTINGS

Project: _____

Fixture Type: _____


Location: _____

Contact/Phone: _____

PRODUCT DESCRIPTION


Special adapters permit the flexibility of mounting trac lights in various ways to meet special requirements.

Line Voltage Monopoint Adapters




**R40N WH, R40N BL,
R40N SL, R40N BZ**

Monopoint Adapter. Mounts directly to outlet box. Accepts one 120V Juno trac fixture.




**T40F WH, T40F BL, T40F
SL**

Flush Monopoint Adapter. Mounts directly to outlet box. Accepts one 120V Juno trac fixture with standard size trac adapter.




**T41N WH, T41N BL,
T41N SL**

Duo-Point Adapter. Mounts directly to an outlet box. Accepts two 120V Juno trac fixtures.




T42N WH, T42N BL

Weighted Base. For portable use. Supplied with 8' cord and plug. Accepts one 120V Juno trac fixture.




T46

Clamp/Monopoint Adapter. Clamps to pipe or planking up to 2 1/2" thick. Accepts one 120V Juno trac fixture. Supplied with 8' three-wire cord and plug.



T45 WH, T45 BL


Pin-Up/Monopoint Adapter. Supplied with 8' cord and plug. Accepts one 120V Juno trac fixture with standard size trac adapter.



T57N WH

Monopoint Line Voltage Cover. Attaches one 120V trac fixture directly to Juno's 6" recessed universal housings.

Line Voltage Coil - Cord Clamp-Ons



T132 WH, T132 BL

120V Monopoint with trac adapter for electrical connection to Trac. Accepts one 120V Juno trac fixture with standard size trac adapter. 2' Coil Cord extends to 5'. 1-3/4" Clamp opening.

T133 WH, T133 BL

120V Monopoint with male plug (120V) attaches to receptacle. Accepts one 120V Juno trac fixture with standard size trac adapter. 2' Coil Cord extends to 5'. 1-3/4" Clamp opening.

Line Voltage Extension Wands




TEW

Line Voltage Extension Wands (12", 18", 24", 36", 48") - For use with one or two circuit trac and line voltage monopoints. Accepts one 120V Juno trac fixture with standard size trac adapter. WH, BL, SL

TEWS

24" Wand with Slope Adapter. Accepts one 120V Juno trac fixture with standard size trac adapter. WH, BL, SL


Line Voltage Sloped Ceiling Adapter



**T95 WH, T95 BL, T95
SL, T95 BZ**

Sloped Ceiling Adapter. Attaches to trac, permitting Trac-Master or Trac-Lites R Series Trac fixtures with standard size trac adapter to be hung vertically from sloped ceiling. 90° maximum adjustable.

Low Voltage Monopoint Adapter



**R58 WH, R58 BL, R58
SL, R58 BZ**

Monopoint Adapter for T537, T538 or Trac-Lites R Series Low-Voltage Power Packs. Mounts directly to outlet box. Adapter is offset to accept all Power Pack styles. Power Pack latch locks in detent.

Specifications subject to change without notice.

