



Tape Measures

Tape Measures-Steel with High-Visibility Case

- High-visibility, high-impact orange case makes it easy to find in a tool box, pouch and on the jobsite
- 16" stud markings and 19.2" truss markings



928-25HV

Cat. No.	Blade Length	Width	Weight
928-25HV	25 ft. (7.6 m)	1" (25.4 mm)	16 oz. (454 g)

Tape Measure Holders

- Klein offers a complete selection of leather or nylon Tape Holders and Pouches



Tape Measure	Holder Cat. No.	Description	Overall Size	Weight
86216, 86315	5195	Medium Leather Pouch	4-1/2" x 7" (114 mm x 178 mm)	2.9 oz. (82 g)
	5707	Nylon Tape Measure Clip/Holder	4-1/8" x 3-3/4" (104 mm x 95 mm)	1.6 oz. (45 g)
86125, 86225, 86375	5196	Large Leather Pouch	5" x 7" (127 mm x 178 mm)	3.4 oz. (95 g)
	5707	Nylon Tape Measure Clip/Holder	4-1/8" x 3-3/4" (104 mm x 95 mm)	1.6 oz. (45 g)
	5195TT	Tape Measure Holder with Ring	3" x 3.5" (76 mm x 89 mm)	1.6 oz. (45 g)
86230	5196	Large Leather Pouch	5" x 7" (127 mm x 178 mm)	3.4 oz. (95 g)
	5707	Nylon Tape Measure Clip/Holder	4-1/8" x 3-3/4" (104 mm x 95 mm)	1.6 oz. (45 g)
	5712	Tape Measure Holder with Ring	8-1/4" x 4-1/2" (210 mm x 114 mm)	3.8 oz. (109 g)

Laser Measuring Tools

Laser Distance Mesurer

- Meter provides measurements up to 65 ft. (19.8 m) in distance, at an accuracy of + or - 1/16" (1.6 mm)
- Quickly calculates length, area, volume, and indirect measurements with large, easy-to-read buttons
- Offers the option of one-touch, single-distance measurement and continuous measurement
- Depth gauge stick flips out to measure from inside corners or channels
- Highly visible backlit display
- Provides both fractional (imperial) and metric readings
- Memory stores last 20 measurements
- Includes handy carrying pouch to keep until safe when not in use

NEW!



93LDM65

Cat. No.	Batteries	Height	Width	Depth	Weight
93LDM65 NEW!	2 x AAA	4-1/2" (114.3 mm)	2" (50.8 mm)	1-3/8" (34.9 mm)	5.1 oz. (145 g)

See page 310 for additional information on warnings.

