



WIRE BASKET SUPPORTS

FEATURES

- Allows wire basket to be suspended from threaded rod without strut
- Spring steel clip installs easily without tools and holds the basket tray securely
- Once installed, low profile clip is designed to minimize damage to the cables in the basket during pulling or maintenance
- Allows installers to prefabricate complex assemblies

WIRE BASKET SUPPORT CLIP

Wire Basket Supports clip to the sides of standard wire basket tray, eliminating the need for strut channels when supporting wire baskets with threaded rod. Multiple variations are available to suit most installations, and enable quick installation and adjustment of multi-level trapeze assemblies.





Material: Spring Steel
Finish: nVent CADDY ARMOUR

Part Number	Article Number	Hole Size HS	A	Diameter Ø	Static Load F
WBS2	182019	0.54"	1" – 1 1/4"	0.14" – 0.24"	120 lb

WIRE BASKET SUPPORT CLIP, RETROFIT

- Slotted design allows wire basket to be installed above an existing trapeze




Material: Spring Steel
Finish: Armour

Part Number	Article Number	Hole Size HS	A	Diameter Ø	Static Load F
WBS1	182015	0.4"	1" – 1 1/4"	0.14" – 0.24"	120 lb

WIRE BASKET SUPPORT CLIP WITH NUT

- Pre-rievted nut eliminates the need for additional hardware




Material: Spring Steel; Steel
Finish: Armour; Electrogalvanized

Part Number	Article Number	Rod Size RS	Diameter Ø	A	Static Load F
WBS37	182023	3/8"	0.14" – 0.24"	1" – 1 1/4"	120 lb

CADDY ROD LOCK WIRE BASKET SUPPORT CLIP

- Easy "push-to-install" design allows installers to simply push the threaded rod through the mounting hole, instantly holding it in position




Material: Spring Steel; Steel
Finish: Armour; Electrogalvanized

Part Number	Article Number	Rod Size RS	Diameter Ø	A	Static Load F
WBS37RL	182018	3/8"	0.14" – 0.24"	1" – 1 1/4"	120 lb

WIRE BASKET SIDE MOUNT CLIP

- Threaded hole allows for attachment of J-Hooks or electrical boxes



Material: Spring Steel Finish: Armour

Part Number	Article Number	Rod Size RS	Diameter Ø	A	Static Load F
WBSH25	182012	1/4"	0.14" – 0.24"	1" – 1 1/4"	120 lb



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

WARNING: nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at nVent.com/ERICO and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

©2018 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

Caddy-DS-D1284S-D163LT17NAEN-EN-1805