

Replacing OFL LED Floodlights



	OFL1 P1	OFL1 P2	Lithonia TFX1 LED
Lumens	2,300	4,450	7,300
Wattage	21W	45W	54W
Efficacy (LPW)	110	99	135
DLC	Standard	Standard	Premium

Replacing OFL LED Floodlights



	OFL2 P2	OFL2 P3	Lithonia TFX2 LED	Lithonia TFX2 LED
Lumens	12,200	16,500	13,200	25,600
Wattage	114W	151W	94W	188W
Efficacy (LPW)	108	110	140	141
DLC	Standard	Standard	Premium	Premium



OFL to TFX Equivalency Chart

OFL LED - To Be Phased Out		TFX LED Equivalent	
CI Code	Description	CI Code	Description
*235M68	OFL1 LED P1 40K MVOLT THK DDBXD M4	*2552M5	TFX1 LED 40K MVOLT THK DDBXD M6
*235M6K	OFL1 LED P1 40K MVOLT YK DDBXD M4	*2552M6	TFX1 LED 40K MVOLT YK DDBXD M6
*2539EC	OFL1 LED P1 40K THK DDBXD PROMO	*2552M5	TFX1 LED 40K MVOLT THK DDBXD M6
*235M6F	OFL1 LED P1 50K MVOLT THK DDBXD M4	*2581FF	TFX1 LED 50K MVOLT THK DDBXD
*235M6N	OFL1 LED P1 50K MVOLT YK DDBXD M4	*2552M6	TFX1 LED 40K MVOLT YK DDBXD M6
*235M6P	OFL1 LED P2 40K MVOLT THK DDBXD M4	*2552M5	TFX1 LED 40K MVOLT THK DDBXD M6
*235M71	OFL1 LED P2 40K MVOLT YK DDBXD M4	*2552M6	TFX1 LED 40K MVOLT YK DDBXD M6
*2539EG	OFL1 LED P2 40K YK DDBXD PROMO	*2552M6	TFX1 LED 40K MVOLT YK DDBXD M6
*235M6T	OFL1 LED P2 50K MVOLT THK DDBXD M4	*2581FF	TFX1 LED 50K MVOLT THK DDBXD
*235M70	OFL1 LED P2 50K MVOLT THK DDBXD SAMPLE CASE	*257X3S	TFX LED SAMPLE CASE
*251N4N	OFL1 LED P2 50K MVOLT YK DDBXD HP17 M4	*2552M6	TFX1 LED 40K MVOLT YK DDBXD M6
*235M72	OFL1 LED P2 50K MVOLT YK DDBXD M4	*2552M6	TFX1 LED 40K MVOLT YK DDBXD M6
*235MA7	OFL2 LED P2 40K 347 IS DDBXD M2	*2552MK	TFX3 LED 40K HVOLT IS DDBXD
*235MAC	OFL2 LED P2 40K 347 YK DDBXD M2	*2552ML	TFX3 LED 40K HVOLT YK DDBXD
*235M9Y	OFL2 LED P2 40K MVOLT IS DDBXD M2	*2552MC	TFX2 LED 40K MVOLT IS DDBXD
*235MA4	OFL2 LED P2 40K MVOLT YK DDBXD M2	*2552ME	TFX2 LED 40K MVOLT YK DDBXD
*2539EJ	OFL2 LED P2 40K YK DDBXD PROMO	*2552ME	TFX2 LED 40K MVOLT YK DDBXD
*235MA8	OFL2 LED P2 50K 347 IS DDBXD M2	*2552MK	TFX3 LED 40K HVOLT IS DDBXD
*235MAE	OFL2 LED P2 50K 347 YK DDBXD M2	*2552ML	TFX3 LED 40K HVOLT YK DDBXD
*235MA2	OFL2 LED P2 50K MVOLT IS DDBXD M2	*2581FG	TFX2 LED 50K MVOLT IS DDBXD
*235MA6	OFL2 LED P2 50K MVOLT YK DDBXD M2	*2581FK	TFX2 LED 50K MVOLT YK DDBXD
*235MAR	OFL2 LED P3 40K 347 IS DDBXD M2	*2552MK	TFX3 LED 40K HVOLT IS DDBXD
*235MAU	OFL2 LED P3 40K 347 YK DDBXD M2	*2552ML	TFX3 LED 40K HVOLT YK DDBXD
*235MAF	OFL2 LED P3 40K MVOLT IS DDBXD M2	*2552MC	TFX2 LED 40K MVOLT IS DDBXD
*235MAJ	OFL2 LED P3 40K MVOLT YK DDBXD M2	*2552ME	TFX2 LED 40K MVOLT YK DDBXD
*2539ER	OFL2 LED P3 40K YK DDBXD PROMO	*2552ME	TFX2 LED 40K MVOLT YK DDBXD
*235MAT	OFL2 LED P3 50K 347 IS DDBXD M2	*2552MK	TFX3 LED 40K HVOLT IS DDBXD
*235MAV	OFL2 LED P3 50K 347 YK DDBXD M2	*2552ML	TFX3 LED 40K HVOLT YK DDBXD
*235MAH	OFL2 LED P3 50K MVOLT IS DDBXD M2	*2581FG	TFX2 LED 50K MVOLT IS DDBXD
*235MAP	OFL2 LED P3 50K MVOLT YK DDBXD M2	*2581FK	TFX2 LED 50K MVOLT YK DDBXD