

# TFX LED Floodlights

## Powerful yet affordable solutions for replacing HID floodlights

TFX LED floodlights are cost-effective, energy-efficient, long-life solutions that replace metal halide floodlights without skimping on lumens. With up to 146 lumens per watt, these products provide more light with less power consumption, delivering over 74% energy savings without compromising on illumination. With an expected service life of over ten years and excellent LED lumen maintenance, these floodlights will avoid the multiple lamp changes associated with the metal halide luminaires they replace.

### The Configurations You Need:

TFX LED floodlights have a wide flood distribution that matches that of most metal halide luminaires they are designed to replace. Threaded knuckle, yoke and integral slipfitter options make installation easy. 4000K and 5000K color temperature options provide flexibility to meet the specific needs of each job site.

### Always in Stock

All TFX LED floodlights are stocked in multiple regional warehouses throughout the country. Select configurations are also featured in the Contractor Select® program.

### A Trusted Name

Lithonia Lighting - *The Best Value in Lighting™* is a brand of Acuity Brands Lighting (NYSE: AYI). Products, delivery and support that you can count on.



### Quick Facts:

- Four sizes deliver 7,300 to 41,700 lumens
- Replace 70W to 1000W metal halide
- Up to 146 lumens per watt
- DLC Premium listed
- 5-Year limited warranty

# TFX LED Floodlight Luminaires

## TFX LED Floodlight Family

### Four Sizes:



	TFX1	TFX2	TFX3	TFX4
HID Replacement Wattage	150W	250W	400W	1000W
Lumens	7,300 lumens	13,200 lumens	25,600 lumens	41,000 lumens
Input Power	54W	94W	188W	296W
Efficacy (LPW)	135	140	141	139
Mounting Options	Knuckle, Yoke	Slipfitter, Yoke	Slipfitter, Yoke	Slipfitter, Yoke

## Ordering Information

### 4000K Stock Configurations

Luminaire	HID Replacement Wattage	Lumen Output	Input Power	Voltage	Mounting	Finish	Catalog Number	CI Code	UPC Code
TFX1	150W	7,300	54W	MVOLT (120V-277V)	Knuckle	Bronze	TFX1 LED 40K MVOLT THK DDBXD	*2552M5	193047670173
					Yoke		TFX1 LED 40K MVOLT YK DDBXD	*2552M6	193047670180
				MVOLT (120V-277V)	Knuckle	White	TFX1 LED 40K MVOLT THK WHXD	*2552M7	193047670197
					Yoke		TFX1 LED 40K MVOLT YK WHXD	*2552MA	193047670227
TFX2	250W	13,200	94W	MVOLT (120V-277V)	Slipfitter	Bronze	TFX2 LED 40K MVOLT IS DDBXD	*2552MC	193047670241
					Yoke		TFX2 LED 40K MVOLT YK DDBXD	*2552ME	193047670234
TFX3	400W	25,600	188W	MVOLT (120V-277V)	Slipfitter	Bronze	TFX3 LED 40K MVOLT IS DDBXD	*2552MF	193047670265
					Yoke		TFX3 LED 40K MVOLT YK DDBXD	*2552MJ	193047670258
		27,330		HVOLT (347V-480V)	Slipfitter		TFX3 LED 40K HVOLT IS DDBXD	*2552MK	193047670289
					Yoke		TFX3 LED 40K HVOLT YK DDBXD	*2552ML	193047670296
TFX4	1000W	41,000	296W	MVOLT (120V-277V)	Slipfitter	Bronze	TFX4 LED 40K MVOLT IS DDBXD	*2552MM	193047670302
					Yoke		TFX4 LED 40K MVOLT YK DDBXD	*2552MN	193047670326
		41,700		HVOLT (347V-480V)	Slipfitter		TFX4 LED 40K HVOLT IS DDBXD	*2552MR	193047670333
					Yoke		TFX4 LED 40K HVOLT YK DDBXD	*2552MS	193047670340

### 5000K Stock Configurations\*

Luminaire	HID Replacement Wattage	Lumen Output	Input Power	Voltage	Mounting	Finish	Catalog Number	CI Code	UPC Code
TFX2	250W	13,200	94W	MVOLT (120V-277V)	Slipfitter	Bronze	TFX2 LED 50K MVOLT IS DDBXD	*2581FG	193048041545
					Yoke		TFX2 LED 50K MVOLT YK DDBXD	*2581FK	193048041552
TFX4	1000W	41,000	296W	MVOLT (120V-277V)	Slipfitter	Bronze	TFX4 LED 50K MVOLT IS DDBXD	*25826T	193048047493
					Yoke		TFX4 LED 50K MVOLT YK DDBXD	*25826X	193048047561
		41,700		HVOLT (347V-480V)	Slipfitter		TFX4 LED 50K HVOLT IS DDBXD	*25827C	193048047547
					Yoke		TFX4 LED 50K HVOLT YK DDBXD	*25827F	193048047578

\* additional configurations in progress

### Part of a Complete Solution:

The TFX LED floodlights are part of a complete floodlighting solution from Lithonia Lighting. QTE LED floodlights are the ideal solution for replacing the huge installed base of quartz halogen and low-wattage metal halide floodlights, providing a long-life, energy-efficient solution at an exceptionally low initial cost. For the specification market, the North-American-made D-Series LED floods are highly configurable, offering a wide selection of optical distributions, lumen packages, CCT's, mounting configurations and colors.



QTE LED

DSXF LED

Visit [www.lithonia.com](http://www.lithonia.com) for more information