

# T4V 250 TMD 32-320 3p F FC 1150V AC



Products → Low Voltage Products and Systems → Circuit Breakers → Moulded Case Circuit Breakers → Tmax T

## General Information

<b>Extended Product Type:</b>	T4V 250 TMD 32-320 3p F FC 1150V AC
<b>Product ID:</b>	1SDA063410R1
<b>EAN:</b>	8015644660192
<b>Catalog Description:</b>	T4V 250 TMD 32-320 3p F FC 1150V AC
<b>Long Description:</b>	C.BREAKER TMAX T4V 250 1150V AC FIXED THREE-POLE WITH FRONT TERMINALS FOR CABLE Cu AND THERMOMAGNETIC RELEASE TMD R 32-320 A

## Ordering

<b>EAN:</b>	8015644660192
<b>Minimum Order Quantity:</b>	1 piece
<b>Customs Tariff Number:</b>	85352100

## Dimensions

<b>Product Net Weight:</b>	1 kg
----------------------------	------

## Container Information

<b>Package Level 1 Units:</b>	1 piece
-------------------------------	---------

## Additional Information

<b>Number of Poles:</b>	3
<b>Power Loss:</b>	at Rated Operating Conditions per Pole 3.7 W
<b>Product Main Type:</b>	SACE Tmax T
<b>Product Name:</b>	Moulded Case Circuit Breaker
<b>Product Type:</b>	CB
<b>Rated Current (I<sub>n</sub>):</b>	Main Circuit 32 A
<b>Rated Operational Voltage:</b>	1150 V AC 1000 V DC
<b>Rated Service Short-Circuit Breaking Capacity (I<sub>cs</sub>):</b>	(1000 V AC) 12 kA
<b>Rated Ultimate Short-Circuit Breaking Capacity (I<sub>cu</sub>):</b>	(415 V AC) 200 kA (1000 V AC) 20 kA
<b>Rated Uninterrupted Current (I<sub>u</sub>):</b>	250 A
<b>Release Type:</b>	TM
<b>Standards:</b>	IEC

<b>Sub-type:</b>	T4
<b>Terminal Connection Type:</b>	Fixed Circuit-Breakers Front for Copper Cables
<b>Version:</b>	F

## Certificates and Declarations (Document Number)

<b>Data Sheet, Technical Information:</b>	1SDC210015D0208
<b>Declaration of Conformity - CE:</b>	1SDL000165R0004
<b>GL Certificate:</b>	1SDL000163R0061
<b>Instructions and Manuals:</b>	1SDH000457R0001

## Classifications

<b>ETIM 4:</b>	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
<b>ETIM 5:</b>	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
<b>ETIM 6:</b>	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
<b>Object Classification Code:</b>	Q

