

Wallplates & Weather Resistant Covers









Decorator Wallplates

All nylon decorator wallplates feature pre-inserted captive screws for faster assembly, up to six-gang. No more dropped or lost screws.

- ◆ Virtually unbreakable nylon.
- ◆ Curved corners blend into any interior.
- ◆ Reinforcement ribs for stiffness.
- ◆ Smooth wallplate for easy cleaning.
- ◆ UL Listed E92074, CSA Certified.

Wallplates & Weather Resistant Covers

Decorator Wallplates

| Description |   | Color | Nylon Standard | Nylon Mid-Size | Material | Metal Catalog No. |
|--|---|--|---|--|--|------------------------------------|
| 1-Gang, 1-Decorator  | | Almond Black Brown Gray Ivory Light Almond White | NP26AL NP26BK NP26 NP26GY NP26I NP26LA NP26W | NPJ26AL NPJ26BK NPJ26 NPJ26GY NPJ26I NPJ26LA NPJ26W | Brass Brass Plated Chrome Stainless Steel | SB26 SBP26 SCH26 SS26 |
| 2-Gang, 2-Decorator  | | Almond Black Brown Gray Ivory Light Almond White | NP262AL NP262BK NP262 NP262GY NP262I NP262LA NP262W | NPJ262AL NPJ262BK NPJ262 NPJ262GY NPJ262I NPJ262LA NPJ262W | Brass Brass Plated Chrome Stainless Steel | SB262 SBP262 SCH262 SS262 |
| 3-Gang, 3-Decorator  | | Almond Black Brown Gray Ivory Light Almond White | NP263AL NP263BK NP263 NP263GY NP263I NP263LA NP263W | NPJ263AL NPJ263BK NPJ263 NPJ263GY NPJ263I NPJ263LA NPJ263W | Brass Brass Plated Chrome Stainless Steel | SB263 SBP263 — SS263 |
| 4-Gang, 4-Decorator  | | Almond Black Brown Gray Ivory Light Almond White | NP264AL NP264BK NP264 NP264GY NP264I NP264LA NP264W | NPJ264AL NPJ264BK NPJ264 NPJ264GY NPJ264I NPJ264LA NPJ264W | Brass Brass Plated Chrome Stainless Steel | SB264 — — SS264 |
| 5-Gang, 5-Decorator  | | Almond Black Brown Gray Ivory Light Almond White | NP265AL NP265BK NP265 NP265GY NP265I NP265LA NP265W | — — — — — — — | Brass Brass Plated Chrome Stainless Steel | SB265 — — SS265 |
| 6-Gang, 6-Decorator  | | Almond Black Brown Gray Ivory Light Almond White | NP266AL NP266BK NP266 NP266GY NP266I NP266LA NP266W | — — — — — — — | Brass Brass Plated Chrome Stainless Steel | SB266 — — SS266 |