



Compatible with Hubbell Labeling System, see page U7.

- UL Listed for Power and Low-Voltage with Label Fields
- Nylon Plates Virtually Unbreakable
- ANSI/TIA-606-B Compliant



### Specifications

- IFP126OW is the only decorator plate in the industry that is UL Listed for power and low-voltage with label fields
- Integrates with all Hubbell keystone connections (AV, data and fiber)
- ISF frames available in 2-, 3-, 4- and 6-port configurations

### Decorator Wallplates

#### Standard, Nylon

Gangs	1-Gang	2-Gang	3-Gang	4-Gang	5-Gang	6-Gang
Catalog No.	<b>NP26xx</b>	<b>NP262xx</b>	<b>NP263xx</b>	<b>NP264xx</b>	<b>NP265xx</b>	<b>NP266xx</b>

xx = Color: **AL** (Almond), **BK** (Black), **GY** (Gray), **I** (Ivory), **LA** (Light Almond), **OW** (Office White), and **W** (White).  
Light Almond is the same color as Office White. See color chart on page V30.

#### Midsize, Nylon

Catalog No.	<b>NPJ26xx</b>	<b>NPJ262xx</b>	<b>NPJ263xx</b>	<b>NPJ264xx</b>	–	–
-------------	----------------	-----------------	-----------------	-----------------	---	---

xx = Color: **AL** (Almond), **BK** (Black), **GY** (Gray), **I** (Ivory), **LA** (Light Almond).

#### Snap-On\*

Catalog No.	<b>RCW1xx</b>	<b>RCW2xx</b>	<b>RCW3xx</b>	<b>RCW4xx</b>	<b>RCW5xx</b>	<b>RCW6xx</b>
-------------	---------------	---------------	---------------	---------------	---------------	---------------

xx = Color: **AL** (Almond), **I** (Ivory), **LA** (Light Almond), **W** (White).

### Decorator and IFP Cover Plates

#### Decorator

Gangs	1-Gang	1-Gang	2-Gang	2-Gang
Material	Brass	Stainless Steel	Brass	Stainless Steel
Catalog No.	<b>SB26</b>	<b>SS26</b>	<b>SB262</b>	<b>SS262</b>

#### IFP Decorator with Label Fields

Color	Almond	Gray	Office White	White
Catalog No.	<b>IFP126AL</b>	<b>IFP126GY</b>	<b>IFP126OW</b>	<b>IFP126W</b>



NP26OW



RCW1I



SS262



IFP126OW

### Decorator Outlet Frames, Unloaded

Ports	2-Port	3-Port	4-Port	6-Port	Blank
Unit Package	1 per bag	1 per bag	1 per bag	1 per bag	1 per bag
Catalog No.	<b>ISF2xx</b>	<b>ISF3xx</b>	<b>ISF4xx</b>	<b>ISF6xx</b>	<b>NS620xx*</b>

xx = Color: **AL** (Almond), **BK** (Black), **EI** (Electric Ivory), **GY** (Gray), **LA** (Light Almond), **OW** (Office White), and **W** (White).  
Light Almond is the same color as Office White. See color chart on page V30.

\*Available in Almond and White only.