
DIGITAL AUDIO TWO-ROOM EXPANSION KIT, WHITE

AU7052-WH | [On-Q](#)



FEATURES & BENEFITS

The AU7052-WH is a two-room Digital Audio Expansion Kit. Conveniently supplying all of the core components necessary to add two new rooms of audio onto an existing Digital Audio System, this kit comes complete with (2) AU7010-WH Digital Audio Amplified Keypads, (1) AU7004 Digital Audio Expansion Module, (1) PW1020 Digital Audio Power Distribution Module, and (1) PW1060 Power Supply.

Check out the [Digital Audio mobile app](#).



- Expands an existing Digital Audio System to two additional rooms
- Comes complete with all core components, including: (2) Digital Audio Amplified Keypads; (1) AU7004 Digital Audio Expansion Module; (1) PW1020 Digital Audio Power Distribution Module; and, (1) PW1060 Power Supply
- Provides 20 watts of Class D power per zone
- Compatible with Digital Audio source components for listening variety
- Conveniently controllable through both included keypads as well as free, intuitive Android or iOS apps for smartphones and tablets
- Provides all core components needed to add two new rooms to an existing system, for simplified expansion
- Simple setup using smartphone or tablet, no PC required

*Streaming services subject to geographic availability. Service subscriptions may be required.

SPECIFICATIONS

GENERAL INFO

Cable Type: Connect Cat5e or better and speaker wire 18-16 gauge.

Color: White

Size: 8.25" x 8.25" x 13.5"

Termination: 918.84 cu. in.

Connection Type: RJ45 connections and removeable pheonix screw down terminals

Type: Low Voltage, Audio System
Special Features: Digital Audio Two-Room Expansion Kit
Style: Decorator Keypad; Structured wiring cabinet (not included)

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
FCC Standard: Yes
UL Standard: Yes

DIMENSIONS

Depth (Metric): 342.9mm
Depth (US): 13.5"
Width (Metric): 209.55mm
Width (US): 8.25"
Primary Packaging Weight (Metric): 1.95 kg
Product Weight (Metric): 1.95 kg
Product Weight (US): 4.3 lbs
Volume: 918.84 cu. in.
Weight: 4.3 lbs
Height: 8.25"

TECHNICAL INFORMATION

Connection Method: Ethernet network
Mounting: Wall Mount/Enclosure Mount
Power Requirements: 24 VDC 60W Power Supply / 12 VDC 18W Power Supply
Supported Standards: FCC, UL, RoHS
Watts: 20W 8Ω
Connection Location: Data Control Interface: Ethernet/Digital Keypad

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA