

**JUNO**<sup>®</sup>**TRAC-MASTER**<sup>®</sup>

Fixture Accessories

**LIGHT CONTROL ACCESSORIES**

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact/Phone: \_\_\_\_\_

**PRODUCT DESCRIPTION**

A wide variety of functional accessories are compatible with most Juno trac fixtures. Refer to fixture specification sheet to confirm compatibility.

**Louvers**

Visually shields lamp and reduces glare.



Series	Diameter
<b>HCLBL</b> (With hexagonal cells)	<b>138</b> 2.75" Diameter
	<b>175</b> 1.75" Diameter
	<b>200</b> 2" Diameter
	<b>275</b> 2.75" Diameter
	<b>300</b> 3" Diameter
	<b>375</b> 3.75" Diameter
	<b>469</b> 4-11/16" Diameter



<b>CCLBL</b> (With square cells)	<b>375</b> 3.75" Diameter
	<b>469</b> 4-11/16" Diameter
	<b>550</b> 5.5" Diameter



<b>CBLBL</b> <b>CBLSL</b> <b>CBLWH</b>	<b>RECT2</b> Rectangular 7" X 4"
--	----------------------------------

**Snoot**

Visually shields lamp and reduces glare.



Series	Diameter
<b>SNOOTBL</b>	<b>175</b> 1.75" Diameter
	<b>200</b> 2" Diameter
	<b>300</b> 3" Diameter
	<b>375</b> 3.75" Diameter
	<b>469</b> 4-11/16" Diameter

<b>SNOOTBL</b> <b>SNOOTSL</b> <b>SNOOTWH</b>	<b>390</b> 3.9" Diameter
--	--------------------------

<b>SNOOTBL</b> <b>SNOOTSL</b> <b>SNOOTWH</b>	<b>RECT2</b> Rectangular 7" X 4"
--	----------------------------------

**Eyebrow**

Reduces uplight, visually shields lamp and reduces glare.



Series	Diameter
<b>EYEBROWBL</b>	<b>200</b> 2" Diameter
	<b>300</b> 3" Diameter
	<b>375</b> 3.75" Diameter
	<b>469</b> 4-11/16" Diameter
	<b>RECT2</b> Rectangular 7" X 4"

**Cross Baffle**

Visually shields lamp and reduces glare.



Series	Diameter
<b>XB AFLBL</b>	<b>375</b> 3.75" Diameter
	<b>469</b> 4-11/16" Diameter

**Barn Doors**

Adjustable doors control glare. Attaches to fixture.



**T71BL 375**  
Black Barn Doors. For trac fixtures T303, T313, T326, T393, T423  
Accepts 3 3/4" diameter accessories.

**T72BL 469**  
Black Barn Doors. For trac fixtures T305, T315, T327, T338, T340, T395, T425.  
Accepts 4 11/16" diameter accessories.

**T73BL 550**  
Black Barn Doors. For trac fixtures T307, T317, T328, T342, T397, T427.  
Accepts 5 1/2" diameter accessories.

**T73WH 550**  
White Barn Doors. For trac fixtures T307, T317, T328, T342, T397, T427.  
Accepts 5 1/2" diameter accessories.

**T74BL 175**  
Black Barn Doors. For Flex12 TFG116, TFP116 and Trac12 TL109, TL116, TLP116,  
Wishbone T480, Delta 200 T216, TP216 and Mini Spots T430, T431 and T442.  
Accepts 1 3/4" diameter accessories.

**TBDR BLCK 375**  
Black Barn Doors. For various trac fixtures including T254L, T262L, T263L, T385L  
and T387L. Accepts 3 3/4" diameter accessories.

**TBDR BLCK 440**  
Black Barn Doors. For various trac fixtures including T271L and T272L. Accepts  
4 11/16" diameter accessories.

**TBDR BLCK 469**  
Black Barn Doors. For various trac fixtures including T209L, T255L, T265L and  
T267L. Accepts 4 11/16" diameter accessories.

**TBDR BLCK RECT2**  
Black Barn Doors. For various rectangular trac fixtures including T258L, T259L and  
T260L.

**TW71BL 375**  
Black Barn Doors. For Wireform<sup>®</sup> trac fixtures T435.  
Accepts 3 3/4" diameter accessories.

Specifications subject to change without notice.


# TRAC-MASTER®

Fixture Accessories

## LIGHT CONTROL ACCESSORIES

### Color Filters


Series	Diameter	Color Filter
<b>CGF</b>	<b>175</b> 1.75" Diameter	<b>MPINK</b> Medium Pink
	<b>200</b> 2" Diameter	<b>WRED</b> Warm Red
	<b>275</b> 2.75" Diameter	<b>DLTBLUE</b> Daylight Blue
	<b>300</b> 3" Diameter	<b>MBLU</b> Medium Blue
	<b>375</b> 3.75" Diameter	<b>MAMB</b> Medium Amber
	<b>469</b> 4-11/16" Diameter	<b>MGRN</b> Medium Green
<b>550</b> 5.5" Diameter		



### Dichroic Color Filters

Provides more saturated color than a Color Filter.

Series	Diameter	Color Filter
<b>DGF</b>	<b>175</b> 1.75" Diameter	<b>DRED</b> Red
	<b>200</b> 2" Diameter	<b>MGRN</b> Medium Green
	<b>275</b> 2.75" Diameter	<b>MBLU</b> Medium Blue
	<b>300</b> 3" Diameter	<b>DYEL</b> Yellow
	<b>375</b> 3.75" Diameter	<b>MAGEN</b> Magenta
	<b>469</b> 4-11/16" Diameter	<b>CYAN</b> Cyan



### Dichroic Color Correction Filters

Series	Diameter	Color Filter
<b>DCCF</b>	<b>175</b> 1.75" Diameter	<b>HAL2700</b> Halogen-to-Incandescent
	<b>200</b> 2" Diameter	<b>HIDINC</b> HID-to-Incandescent
	<b>275</b> 2.75" Diameter	<b>HL4250</b> Halogen-to-Daylight
	<b>300</b> 3" Diameter	
	<b>375</b> 3.75" Diameter	
<b>469</b> 4-11/16" Diameter		



### Beam Control Lenses


**Prismatic Spread Glass Lens** Coarse prismatic lens reduces striations and enlarges the beam.

**Linear Spread Glass Lens** Oval pattern linear spread lens directs beam into an elongated oval shape.

**Solite Lens** Eliminates striations without altering size of beam.

**Diffusion Lens** Frosted lens softens the beam and lightly diffuses the pattern.


**UV Filter** Optivex Museum Quality UV Filter. Filters out transmission below 400nm.



Series	Diameter
<b>PRISM</b>	<b>175</b> 1.75" Diameter
<b>LSPREAD</b>	<b>200</b> 2" Diameter
<b>SOLITE</b>	<b>275</b> 2.75" Diameter
<b>DIFF</b>	<b>300</b> 3" Diameter
<b>UVF</b>	<b>375</b> 3.75" Diameter
	<b>469</b> 4-11/16" Diameter

### Accessory Holder

Attaches to fixture.



#### T560BL

For trac fixtures T303, T313, T326, T393, T423.  
Accepts 3 3/4" diameter accessories.

#### T570BL

For trac fixtures T305, T315, T327, T338, T340, T395, T425.  
Accepts 4 11/16" diameter accessories.

#### T580BL

For trac fixtures T307, T317, T328, T342, T397, T427.  
Accepts 5 1/2" diameter accessories.

#### TAH BLCK 469

For trac fixtures T1030, T1031S. Accepts 4 11/16" diameter accessories.

#### TAH BLCK 550

For trac fixture T1038. Accepts 5.5" diameter accessories.

### MR16 Accessory Holder

Attaches to MR16 lamp without the use of tools or clips.



#### T7400BL, T7400SA

For use with Flex12 TF130, TF301, Trac12 TL117, TL130, TL301, Flyback T227, TP216, Universal T401 and Trapezia T630. Accepts up to two 2" media and/or T7470BL, T7470SA Barn Doors.

Series	Diameter
<b>T7400BL</b>	<b>200</b> 2" Diameter
<b>T7400SA</b>	

### Accessory Spring Kits

#### TASK1

For Gimbal16 fixtures. Accepts 2" diameter accessories.

#### TASK2

For Concentricity16 fixtures. Accepts 2" diameter accessories.