


# Hex Nuts



Part #	Size	Description	PKG TYPE	PKG QTY	Weight / M	UPC #
F44833	6-32	HEX NUT	DECIMAL PAK	100	1.96	05999444833
F44834	8-32	HEX NUT	DECIMAL PAK	100	2.58	05999444834
F44835	10-24	HEX NUT	DECIMAL PAK	100	2.97	05999444835
F44839	1/4-20	HEX NUT	DECIMAL PAK	100	6.00	05999444839
F44837	10-32	HEX NUT	DECIMAL PAK	100	3.00	05999444837
F38160	3/8 - 16	HEX NUT	DECIMAL PAK	100	16.00	625912630253
F12130	1/2 - 13	HEX NUT	DECIMAL PAK	100	37.50	625912630161

# Washers & Bolts

Part #	Size	Description	PKG TYPE	PKG QTY	Weight / M	UPC #
F14100	1/4 x 1 ZINC PLATED	FENDER WASHER	JAR	100	21.40	625912630208
F14114	1/4 ID x 1 1/4 OD	FENDER WASHER	JAR	100	3.02	625912630215
F316114	3/16 x 1 - 1/4 ZINC PLATED	FENDER WASHER	JAR	100	14.40	625912630222
F38114	3/8 x 1 - 1/4 ZINC PLATED	FENDER WASHER	JAR	100	31.10	625912630277
F0623FW	#6	FLAT WASHER	BLISTER PAK	100	0.94	625912630116
F0823FW	#8	FLAT WASHER	BLISTER PAK	100	1.25	625912630123
F1023FW	#10	FLAT WASHER	BLISTER PAK	100	2.50	625912630130
F1400FW	1/4 ZINC PLATED	FLAT WASHER	JAR	100	6.20	625912630178
F3800FW	3/8 ZINC PLATED	FLAT WASHER	JAR	100	13.40	625912630246
F1200FW	1/2 ZINC PLATED	FLAT WASHER	JAR	100	30.80	625912630536
F600LW	#6 ZINC	SPLIT LOCKWASHER	JAR	100	0.94	625912636002
F1000LW	#10 ZINC	SPLIT LOCKWASHER	JAR	100	1.30	625912630291
F1400LW	1/4 ZINC PLATED	SPLIT LOCKWASHER	JAR	100	2.20	625912630185
F3800LW	3/8 ZINC PLATED	SPLIT LOCKWASHER	JAR	100	6.00	625912630239
F1200LW	1/2 ZINC PLATED	SPLIT LOCKWASHER	JAR	100	12.90	625912630154
F14201	1/4 - 20x1 GRADE 2	HEX HD BOLT	JAR	100	22.60	625912630192
F381634	3/8 - 16 x 3/4 GRADE 2	HEX HD BOLT	JAR	100	38.00	625912630505
F38161	3/8 - 16 x 1 GRADE 2	HEX HD BOLT	JAR	100	42.90	625912630260
F12131	1/2 - 13 x 1 GRADE 2	HEX HD BOLT	JAR	100	62.90	625912630543

# Anchors & Other Items



Part #	Size	Description	PKG TYPE	PKG QTY	Weight / M	UPC #
F14381	1/4 - 20 (3/8 X 1 HOLE)	DROP-IN ANCHOR	JAR	50	2.33	625912630222
F38121	3/8 - 16 (1/2 X 1 9/16 HOLE)	DROP-IN ANCHOR	JAR	50	3.30	625912630239
F31678	3/16 x 7/8	NAIL-IN ANCHOR	JAR	100	9.10	625912630406
F14111	1/4 x 1	NAIL-IN ANCHOR	JAR	100	18.70	625912630413
F6810L	6-8 x 1	LEAD ANCHOR	JAR	100	14.70	625912630284
F101214	10-12-14 x 3/4	LEAD ANCHOR	JAR	100	18.80	625912630420
F6810	#6-8 x 1" White	PLASTIC ANCHOR	PLASTIC BIN	100	1.25	625912630024
F8101	#8-10 x 1 1/4" Blue	PLASTIC ANCHOR	PLASTIC BIN	100	2.00	625912630031
F10120	#10-12 x 1"	PLASTIC ANCHOR	PLASTIC BIN	100	2.25	625912630437
F81316	White, 8x1, 3/16 Carbide Bit	PAN HEAD ANCHOR KIT	JAR	100	N/A	625912630444
F10114	Blue, 10x1, 1/4 Carbide Bit	PAN HEAD ANCHOR KIT	JAR	100	N/A	625912630451
F14134	1/4 x 1 3/4	STUD WEDGE ANCHOR	JAR	50	31.20	625912630468
F14214	1/4 x 2 1/4	STUD WEDGE ANCHOR	JAR	50	36.80	625912630475
F38214	3/8 x 2 1/4	STUD WEDGE ANCHOR	JAR	50	80.50	625912630482
F38300	3/8 x 3	STUD WEDGE ANCHOR	JAR	50	99.20	625912630499
F142118	1/4 - 2 - 1 1/8	TIE WIRE ANCHOR	PLASTIC BIN	100	34.50	625912630307
F183.T18	1/8" x 3"	SPRING TOGGLE BOLT	PLASTIC BIN	50	16.25	625912630062
F3163.T316	3/16"	SPRING TOGGLE BOLT	PLASTIC BIN	50	25.00	625912630079
F143.T14	1/4" x 3"	SPRING TOGGLE BOLT	PLASTIC BIN	50	34.72	625912630093
F3163	3/16" x 3" + Bolt	DRILLER TOGGLE	PLASTIC BIN	30	51.23	625912630086
F6300	#6	ZINC WALL DRILLER	PLASTIC BIN	100	7.37	625912630048
F8500	#8	ZINC WALL DRILLER	PLASTIC BIN	100	15.75	625912630055
F80000	#8 WHITE PLASTIC	PLASTIC WALL DRILLER	PLASTIC BIN	100	0.40	625912630147
F381618	3/8 - 16 x 1 1/8	ROD COUPLING	PLASTIC BIN	25	3.30	625912630512
F121314	1/2 - 13 x 1 1/4	ROD COUPLING	PLASTIC BIN	25	3.30	625912630529

# Stainless Steel Flat Screws

Part #	Size	Description	PKG TYPE	PKG QTY	UPC #
F65428	6x1/2	18-8 STAINLESS STEEL	DECIMAL PAK	100	05999465428
F65430	6x3/4	18-8 STAINLESS STEEL	DECIMAL PAK	100	05999465430
F65431	6x1	18-8 STAINLESS STEEL	DECIMAL PAK	100	05999465431