

**47690-6**

# Voice, Data, and Video Distribution

**Brand Features**

Use 4-, 6- and 8-way 1GHz Passive Video Splitters and Passive Video Splitter Modules to split digital cable, quality cable TV and off-air signals to 4, 6 or 8 televisions throughout a home or office. The Video Splitter Modules are designed for easy installation in any Leviton 140, 280 or 420 Structured Media Enclosure. The Video Splitters are easily installed in Leviton MDU Enclosures or used in any application where a passive video splitter is needed. These units feature die-cast housings and printed circuit board construction.



**Item Description**

1 x 6 (6-Way) 1 GHz Passive Video Splitter

**Technical Information**

Material Specifications

**Color:** Silver

Mechanical Specifications

**Style Name:** 1X6

**F-Type Inputs:** 1

**F-Type Outputs:** 6

**Frequency Range:** 1 GHz

**AC Power Adapter:** No

Product Features

**Type:** Passive Video Splitter

**Style Name:** 1X6

**Frequency Range:** 1 GHz

**Impedance:** 75 Ohm

**AC Power Adapter:** No

**Color:** Silver

**Standards and Certifications:** Meets all applicable standards

**Warranty:** 2 Year Limited

**UPC Code:** 07847718371

**Country of Origin:** China

Performance Data

**Impedance:** 75 Ohm

**Insertion Loss dB:** 10.0 dB - 12.1 dB

**Return Loss dB Forward:** 6.5 dB - 23.5 dB

**Isolation dB:** 28.9 dB - 37.5 dB

**Features and Benefits**

- Splits Video signals, Outputs for up to 6 televisions.
- Provide digital cable, cable tv and other video services, via coaxial cable to any room in the house.
- Die-cast housing and printed circuit board.
- Use with the Video Amplifier to increase signal quality, analog or standard cable applications only.
- For mounting in Compact Structured Media Enclosures.
- 75 Ohm termination caps included for unused connectors.

**SPECIFICATION SUBMITTAL**

<p><b>JOB NAME:</b></p> <input style="width: 90%; height: 20px;" type="text"/>	<p><b>CATALOG NUMBERS:</b></p> <input style="width: 90%; height: 20px;" type="text"/>	
<p><b>JOB NUMBER:</b></p> <input style="width: 90%; height: 20px;" type="text"/>		

**Leviton Manufacturing Co., Inc.**

201 North Service Road, Melville, NY 11747

Telephone: 1-800-323-8920 · FAX: 1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): 1-800-824-3005

**Leviton Manufacturing of Canada, Ltd.**

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: 1-800-469-7890 ·

FAX: 1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

**Leviton S. de R.L. de C.V.**

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · [www.leviton.com.mx](http://www.leviton.com.mx)

**Visit our Website at: [www.leviton.com](http://www.leviton.com)**

© 2012-2015 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

**Leviton has a global presence.**

If you would like to know where your local Leviton office is located please go to: [www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)

