


## Home 6® Connectors

### APPLICATION

The HOME 6 Connector provides network connections for CAT 6 UTP structured cabling systems in residential applications. The connectors support high megabit applications and meets channel-rated performance according to TIA CAT 6 standards.



### SPECIFICATION

The HOME 6 Connector shall allow wire termination by use of traditional punchdown methods. The wiring color code shall follow T568A scheme, displayed on a label on the connector. The connector body shall be made of fire-retardant plastic with a flammability rating of 94V-0. It shall be compliant with TIA-568-C.2 and FCC part 68, and have cULus certification.

### FEATURES

- Available in seven colors
- T568A wiring
- Individual port configurability allows specification flexibility
- Robust one-piece lead-frame design
- Narrow connector allows high-port density in a small area
- Performance supports high megabit and shared-sheath applications

### DESIGN CONSIDERATIONS

- Use in any QuickPort® housing to support CAT 6 UTP connectivity in surface mount, flush-mount, or modular furniture outlets, or patch panels and patch blocks
- Can be used in conjunction with other QuickPort snap-in modules for voice/data and video applications over UTP, coax and fiber
- To ID ports, use different colored modules for each application

### STANDARDS COMPLIANCE

Meets all applicable standards and listings:

- TIA-568-C.2
- FCC Part 68
- cULus Listed

### PHYSICAL SPECIFICATIONS

Dimensions: .58" H x .63" W x 1.18" D

Materials: Connector body is high-impact fire-retardant plastic, rated UL 94V-0. Spring wire contacts are high-quality phosphor bronze, plated with 50 micro-inches of gold over 100 micro-inches of nickel for lowest contact resistance, maximum life. Connector 110-style IDC contacts are solder-plated phosphor bronze.

### COUNTRY OF ORIGIN

Taiwan

### WARRANTY INFORMATION

For a copy of Leviton product warranties, visit [www.leviton.com](http://www.leviton.com).

#### Leviton Network Solutions

2222 - 222nd St. SE  
Bothell, WA 98021-4416

tel 1-800-824-3005  
tel +1-425-486-2222  
appeng@leviton.com  
www.leviton.com

#### Asia / Pacific

T +1.631.812.6228  
E infoasean@leviton.com

#### Europe

T +33.6.8869.1380  
E infoeurope@leviton.com

#### Canada

T +1.514.954.1840  
E pcservice@leviton.com

#### India / SAARC

T +91.80.4322.5678  
E infoindia@leviton.com

#### Caribbean

T +1.954.593.1896  
E infocaribbean@leviton.com

#### Mexico

T +52.55.5082.1040  
E lsamarketing@leviton.com

#### China

T +852.2774.9876  
E infochina@leviton.com

#### Middle East & Africa

T +971.4.886.4722  
E lmeinfo@leviton.com

#### Colombia


T +57.1.743.6045  
E infocolombia@leviton.com

#### South Korea

T +82.2.3273.9963  
E infokorea@leviton.com

**ELECTRONIC FILES**

For CAD files, typical specs, or technical drawings (.DXF, .DWG, VISIO), visit [www.leviton.com](http://www.leviton.com).



**61HOM-R\*6**

**PART NUMBER**

Description	Part Number
HOME 6® Connector	61HOM-R*6

\*= Colors: Ivory (I), White (W), Grey (G), Black (E), Light Almond (T), Brown (B), Blue (L)



**Leviton Network Solutions**  
2222 - 222nd St. SE  
Bothell, WA 98021-4416

**Asia / Pacific**  
T +1.631.812.6228  
E [infoasean@leviton.com](mailto:infoasean@leviton.com)

**Canada**  
T +1.514.954.1840  
E [pcservice@leviton.com](mailto:pcservice@leviton.com)

**Caribbean**  
T +1.954.593.1896  
E [infocaribbean@leviton.com](mailto:infocaribbean@leviton.com)

**China**  
T +852.2774.9876  
E [infochina@leviton.com](mailto:infochina@leviton.com)

**Colombia**  
T +57.1.743.6045  
E [infocolombia@leviton.com](mailto:infocolombia@leviton.com)

tel 1-800-824-3005  
tel +1-425-486-2222  
[appeng@leviton.com](mailto:appeng@leviton.com)  
[www.leviton.com](http://www.leviton.com)

**Europe**  
T +33.6.8869.1380  
E [infoeurope@leviton.com](mailto:infoeurope@leviton.com)

**India / SAARC**  
T +91.80.4322.5678  
E [infoindia@leviton.com](mailto:infoindia@leviton.com)

**Mexico**  
T +52.55.5082.1040  
E [lsamarketing@leviton.com](mailto:lsamarketing@leviton.com)

**Middle East & Africa**  
T +971.4.886.4722  
E [lmeinfo@leviton.com](mailto:lmeinfo@leviton.com)

**South Korea**  
T +82.2.3273.9963  
E [infokorea@leviton.com](mailto:infokorea@leviton.com)