



Order code	Description	Shape	Base	Volts (V)	Colour	Average life (hrs)
------------	-------------	-------	------	-----------	--------	--------------------

T-3 1/4 - Single chip (6 V, 12-14 V, 24-28 V)

MOL : 1 1/2 in. (26 mm) Dia. : 11/32 in. (9 mm)

62028	LED/A/T31/4/MB/6V	T-3.25	Miniature bayonet (BA9s)	6	Amber	100 000
62031	LED/B/T31/4/MB/6V	T-3.25	Miniature bayonet (BA9s)	6	Blue	100 000
62034	LED/G/T31/4/MB/6V	T-3.25	Miniature bayonet (BA9s)	6	Green	100 000
62037	LED/R/T31/4/MB/6V	T-3.25	Miniature bayonet (BA9s)	6	Red	100 000
61974	LED/WH/T31/4/MB/6V	T-3.25	Miniature bayonet (BA9s)	6	White	100 000
62029	LED/A/T31/4/MB/12V-14V	T-3.25	Miniature bayonet (BA9s)	12-14	Amber	100 000
62032	LED/B/T31/4/MB/12V-14V	T-3.25	Miniature bayonet (BA9s)	12-14	Blue	100 000
62035	LED/G/T31/4/MB/12V-14V	T-3.25	Miniature bayonet (BA9s)	12-14	Green	100 000
62038	LED/R/T31/4/MB/12V-14V	T-3.25	Miniature bayonet (BA9s)	12-14	Red	100 000
62040	LED/WH/T31/4/MB/12V-14V	T-3.25	Miniature bayonet (BA9s)	12-14	White	100 000
62030	LED/A/T31/4/MB/24V-28V	T-3.25	Miniature bayonet (BA9s)	24-28	Amber	100 000
62033	LED/B/T31/4/MB/24V-28V	T-3.25	Miniature bayonet (BA9s)	24-28	Blue	100 000
62036	LED/G/T31/4/MB/24V-28V	T-3.25	Miniature bayonet (BA9s)	24-28	Green	100 000
62039	LED/R/T31/4/MB/24V-28V	T-3.25	Miniature bayonet (BA9s)	24-28	Red	100 000
61970	LED/WH/T31/4/MB/24V-28V	T-3.25	Miniature bayonet (BA9s)	24-28	White	100 000

Cross reference: 12MB, 14MB, 24MB, 28MB, 44, 47, 238, 239, 240, 256, 267, 313, 316, 755, 756, 757, 1408, 1437, 1488, 1810, 1813, 1815, 1816, 1818, 1819, 1820, 1826, 1828, 1829, 1830, 1843, 1847, 1864, 1866, 1873, 1888, 1889, 1891, 1892, 1893, 3796, 3797, 3895.

Order code	Description	Shape	Base	Volts (V)	Colour	Average life (hrs)
------------	-------------	-------	------	-----------	--------	--------------------

T-3 1/4 - Single chip (48 V, 60 V, 120 V)

MOL : 1 1/2 in. (26 mm) Dia. : 11/32 in. (9 mm)

62044	LED/A/T31/4/MB/48V	T-3.25	Miniature bayonet (BA9s)	48	Amber	100 000
62047	LED/B/T31/4/MB/48V	T-3.25	Miniature bayonet (BA9s)	48	Blue	100 000
62050	LED/G/T31/4/MB/48V	T-3.25	Miniature bayonet (BA9s)	48	Green	100 000
62052	LED/R/T31/4/MB/48V	T-3.25	Miniature bayonet (BA9s)	48	Red	100 000
62055	LED/WH/T31/4/MB/48V	T-3.25	Miniature bayonet (BA9s)	48	White	100 000
62045	LED/A/T31/4/MB/60V	T-3.25	Miniature bayonet (BA9s)	60	Amber	100 000
62048	LED/B/T31/4/MB/60V	T-3.25	Miniature bayonet (BA9s)	60	Blue	100 000
62051	LED/G/T31/4/MB/60V	T-3.25	Miniature bayonet (BA9s)	60	Green	100 000
62053	LED/R/T31/4/MB/60V	T-3.25	Miniature bayonet (BA9s)	60	Red	100 000
62056	LED/WH/T31/4/MB/60V	T-3.25	Miniature bayonet (BA9s)	60	White	100 000
62046	LED/A/T31/4/MB/120V	T-3.25	Miniature bayonet (BA9s)	120	Amber	100 000
62049	LED/B/T31/4/MB/120V	T-3.25	Miniature bayonet (BA9s)	120	Blue	100 000
62024	LED/G/T31/4/MB/120V	T-3.25	Miniature bayonet (BA9s)	120	Green	100 000
62054	LED/R/T31/4/MB/120V	T-3.25	Miniature bayonet (BA9s)	120	Red	100 000
62057	LED/WH/T31/4/MB/120V	T-3.25	Miniature bayonet (BA9s)	120	White	100 000

Cross reference: 48MB, 60MB, 90MB, 1828, 1835, SP-105, SP-114, SP-120, SP-121.

*All colours are available upon request.

T-3 1/4 - Single Chip