

Residential Load Centers

Special Purpose Circuit Breakers

60°C / 75°F Conductor Rating

Box Type Terminals

Quick-Make, Quick-Break

Multi-pole Breakers Incorporate Internal Common Trip

Molded Case Switches

UL Listed (Molded Case Switches No. 1087). Without overload or short circuit protection.

Ampere Rating	2-Pole		3-Pole	
	Product Number	List Price GO-138A	Product Number	List Price GO-138
120/240 Volts ac				
60	TQL21Y60	\$51.00	-	-
100	TQL21Y100	\$147.00	-	-
240 Volts ac				
60	TQL22Y60	\$139.00 ¹	TQL32Y60	\$177.00
100	TQL22Y100	\$235.00 ¹	TQL32Y100	\$266.00
Std. Pkg.	5 cartons of 5		5 cartons of 3	

¹GO-138



TQL21Y100

Sub-feed and Feed-thru Lugs

UL Listed

For use in load centers to economically supply power to a subpanel.

Poles	Ampere Rating	Product Number	List Price GO-137A
2	125	THLK2125	\$77.00
3	125	THLK3125	\$107.00
2	150	THLK2150 ²	\$137.00
2	200	THLK2200 ²	\$158.00
3	225	THLK3225 ³	\$250.00

²For use with PowerMark Gold load centers only

³For use with three-phase load centers only. Includes mounting base.



THLK2125

TQ Circuit Breakers

3/4" UL Classified Circuit Breakers for use in *Square D *QO Load Centers.

10 kAIC RMS symmetrical

Ampere Rating	1-Pole		2-Pole	
	Product Number	List Price GO-138Q	Product Number	List Price GO-138Q
15	TQ1115	\$20.25	TQ2115	\$46.00
20	TQ1120	\$20.25	TQ2120	\$46.00
30	TQ1130	\$20.25	TQ2130	\$46.00
40	TQ1140	\$20.25	TQ2140	\$46.00
50	TQ1150	\$20.25	TQ2150	\$46.00
60	-	-	TQ2160	\$46.00
Std. Pkg.	1 carton of 10		1 carton of 5	



THLK2150

Interlocking Circuit Breakers for use in PowerMark Gold Generator Panels

Two breakers required for interlocking.

Ampere Rating	2-Pole	
	Product Number	List Price GO-138A
30	THQL2130GEN	\$238.75
60	THQL2160GEN	\$238.75



TQ1120

*Square D is a registered trademark of SNA Holdings, Inc.

*QO is a registered trademark of the Square D Company.

