

Accessories

Field Installed Kits/Replacement Parts

Filler Plates

Breaker Type	Cat. No.
THQB/THHQB/THQL/THHQL/TEY	TQLFP1
TQD/THQD/TED4/SE/FB	TEDFP1

Endwall Kits

Field installed.
1 each, for
standard 20"w x
5.81"d boxes.

Type	Cat. No.
Blank	ABEW2
Knockout	ABEW2

Breaker Mounting Hardware Kits

For mounting breaker in existing space

Breaker Type	Cat. No.
TED/THED4/SE	ASPTED3P
TQD/THQD	ASPTQD3P
FB	ASPFB12P

Equipment Grounds



AEBG



AEIG



ASPGIBC



AEBGC



AEIGC

Item	Description	Wire Range	Cat. No.
Metal Equipment Ground	Bonded	#14-#8 Cu, #12-#8 Al (small holes); #14-#4 Cu, #6-#4 Al (large holes)	TGL2
	Extruded Bonded	#14-#8 Cu, #12-#8 Al (small holes); #14-#4 Cu, #6-#4 Al (large holes)	EGS12
Aluminum Equipment Ground	Extruded Bonded	(1) #6-350MCM	AEBG
	Extruded Isolated	(2) #6-250MCM	AEIG
	Main Lug	#14-#8 Cu, #12-#8 Al (small holes); #14-#4 Cu, #6-#4 Al (large holes)	TGL2
Copper Equipment Ground	Bonded	#14-#8 Cu, #12-#8 Al (small holes); #14-#4 Cu, #6-#4 Al (large holes)	TGC2
	Extruded Bonded	(1) #4-350MCM	AEBGC
	Extruded Isolated	(1) #6-250MCM	AEIGC
	Insulated Isolated	2/0 max.	ASPGIBC

Bonding Kits

Description	Cat. No.
For Split & Load End Neutral	343L886G16
For 225A Horizontal Neutrals	343L886G13
225A Horizontal Neutral To Convert 3W to 4W	ASP225HNCP
125/225A Horizontal Neutral Conversion from Service Entrance to Non-Service Entrance	ASPHNCPSENOT
125/225A Horizontal Neutral to Convert from Non-Service Entrance to Service Entrance.	ASPHNCPSE

Installation & Maintenance Kit

Order catalog number PROCARE. Kit includes:

- (5) filler plate hardware kits
- (9) bus stud nuts
- (5) MLA1 filler plates
- (2) 225A phase barriers
- (2) feed-thru barriers
- (1) 400/600A phase barrier
- (50) directory cards/rating books
- (50) circuit number strips (1-48)
- (50) circuit number strips (43-84)
- (5) standard locks & keys
- (50) deadfront screws
- (10) AQ/AE front hardware kits
- (10) AD front hardware kits
- (50) service disconnect labels
- (50) main labels

Parts

Description	Cat. No.
Directory Card	139C5612P3
Replacement Lock with Std. Key	569B737P1
Replacement Lock with GE75 Key	569B737P2
Additional Keys for Above Lock	569B737P5
Circuit Numbering Strips 1-48	569B806G1
Circuit Numbering Strips 49-84	569B806G2
Circuit Numbering Strips 85-126	569B806G3
Adhesive Backed Lamicoide Nameplate 3/4" x 3"	315A7190P1
Metal Directory Card Holder	139C5491G1
Directory Card Holder	139C5491P4
Delta Hi-leg Conversion Kit, to Add B-Phase Plug on AL Panels	APHBL
Bolt on AE/AQ Panels	APHBQ
NEMA 3R/12 Tamper Proof Tork Screw Kit	NEMATRIX
2P to 3P TQD Conv. Kit	ASP2PTQD3P
2P to 3P SF Conv. Kit for horizontal subfeed	ASP2PTFJ3P
AD 25 to 65 kAIC Barrier kit	ASP25AD65KA1
Service Entrance Kit	ASPSERENT
2 wire Relay Kit	ASP2WRelay
Yale Lock Kit	ASPYALE47
Corbin Lock Kit	ASPCORBNTU1
2-3 pole TQD Mechanical Interlock	TQDFM1
AQ/AL/AE Rail Bracket	ASPAQLEBKT
Front Flush Adjust Kit	ASPFLUSHADJ
AE Front Mounting Kit	139C5720G3
AQ/AL Front Mounting Kit	139C5720G6
AD Front Mounting Kit	139C5728G9
Front Hinge to Box Mounting Kit	139C5700G6
Front Extension Mounting Kit	139C5700G11

Box Extensions

Bolts to box with or without endwall in place. Extensions can be combined to obtain lengths greater than 18 and 24 inches.

Box Width and Depth	Box Mounting	Box Extension Length (Inches)	Cat. No.
20 x 5.81	Flush	9	ABX2509F
		18	ABX2518F
		24	ABX2524F
	Surface	9	ABX2509S
		18	ABX2518S
		24	ABX2524S
		31	ABX2531S
		37	ABX2537S
		43	ABX2543S
		49	ABX2549S
		55	ABX2555S
		64	ABX2564S
76	ABX2576S		
30 x 5.81	Flush	18	ABX3518F
		24	ABX3524F
	Surface	18	ABX3518S
		24	ABX3524S
30 x 7.81	Flush	18	ABX3718F
		24	ABX3724F
	Surface	18	ABX3718S
		24	ABX3724S

Box Extension Covers Only

10 covers per kit

Description	Cat. No.
9" Covers Surface	ASPABX09S
9" Covers Flush	ASPABX09F
18" Covers Surface	ASPABX18S
18" Covers Flush	ASPABX18F
64" to 76" Covers Surface	ASPABX20S
64" to 76" Covers Flush	ASPABX20F