

Another innovative solution for Wire and Cable Management

# IBERVILLE®



## 2-inch deep shallow rework box

Takes the work  
out of rework  
when 2-1/2 inches  
is too deep.

The Iberville® BC1102LRB, flat-sided shallow rework box is ideally suited for any application where space is limited.

- Flat sides simplify installation, making insertion into drywall opening trouble free
- Low profile – 2 inches deep
- 10 cubic inch capacity
- Ideally suited for applications where space behind drywall is limited
- Gangable device box
- Heavy-duty steel construction for maximum strength and durability
- CSA Certified
- Designed and manufactured in Canada

Flat sides for easy installation

Only 2 inches deep

Gangable for multi-device applications



Thomas & Betts. Your best connection for innovative solutions.

# Iberville® LRB™ family of hassle-free rework boxes



**BC1102-LRB**  
Gangable  
**10.0**  
cu. in.




**BC1104-LRB**  
Gangable  
**12.5**  
cu. in.



**BC1004-LRB**  
Gangable  
**15.0**  
cu. in.



**BC2104-LRB**  
Welded  
**12.5**  
cu. in.



**BC2104-LRB-2**  
Welded 2 gang  
**25.0**  
cu. in.



**BC54151-LD**  
Octagonal with  
"swing arm" brackets  
**15.0**  
cu. in.



**CI820-DX**  
For a solid installation,  
combine the LRB™ family with  
CI820-DX rework bracket



See our installation video for Rework boxes on [www.tnb.ca/video](http://www.tnb.ca/video)



## Iberville® LRB™ Family of Rework Boxes



CAT. NO.	DESCRIPTION	CAPACITY (cu. in.)	PRYOUTS		KNOCKOUTS
			SIDES	BOTTOM	
BC1102-LRB	2 in. deep gangable device box	10.0	4	—	—
BC1104-LRB	2-1/2 in. deep gangable device box	12.5	4	—	—
BC2104-LRB	2-1/2 in. deep welded single gang device box	12.5	4	—	—
BC2104-LRB-2	2-1/2 in. deep welded 2 gang device box	25.0	4	—	—
BC1004-LRB	3 in. deep gangable device box	15.0	4	—	—
BC54151-LD	Octagonal with "sing-arm" brackets	15.0		4	1/2 in. bottom
CI820-DX	Rework bracket for LRB box support	n/a		—	—

### Atlantic Provinces

Thomas & Betts Limited  
Tel.: (902) 450-1307  
Toll Free: 1-877-862-4357  
Fax: (902) 450-1309

### Quebec

Thomas & Betts Limited  
Tel.: (450) 466-1102  
Toll Free: 1-800-465-1399  
Fax: (450) 466-1163

### Ontario

Thomas & Betts Limited  
Tel.: (905) 858-1010  
Toll Free: 1-877-291-7771  
Fax: (905) 858-1080

### Manitoba/Saskatchewan

Thomas & Betts Limited  
Tel.: (604) 598-9811  
Toll Free: 1-866-540-8220  
Fax: (604) 598-9840

### Alberta

Thomas & Betts Limited  
Tel.: (780) 424-7092  
Toll Free: 1-888-664-5666  
Fax: (780) 424-7093  
Toll Free: 1-866-424-4082

### British Columbia

Thomas & Betts Limited  
Tel.: (604) 598-9811  
Toll Free: 1-866-540-8220  
Fax: (604) 598-9840