

Catamount™

Terminals — Now in Convenient, Spillproof, Re-Usable Packaging!

While poly bags keep their contents dry, they don't offer much other protection, and they aren't environmentally friendly. That's why Catamount™ terminals now come in sturdy plastic containers that safeguard the connectors inside against crushing and can be re-used or recycled when empty. T&B is always adding value to its products. With the introduction of a durable plastic container, the value of T&B's Catamount™ terminals has been significantly enhanced. No more lost or spilled terminals because of inadequate packaging.



Vinyl Insulated Ring Terminals

Cat. No.	Wire Range	Bolt Size	Pkg Qty
TV18-6R-XV	22-16	#6	15
TV18-8R-XV		#8	
TV18-10R-XV		#10	
TV14-6R-XV	16-14	#6	15
TV14-8R-XV		#8	
TV14-10R-XV		#10	
TV10-8R-XV	12-10	#8	15
TV10-10R-XV		#10	
TV10-14R-XV		1/4"	



Vinyl Insulated Fork Terminals

Cat. No.	Wire Range	Bolt Size	Pkg Qty
TV18-6F-XV	22-16	#6	15
TV18-8F-XV		#8	
TV14-6F-XV	16-14	#6	15
TV14-8F-XV		#8	
TV14-10F-XV		#10	
TV10-8F-XV	12-10	#8	15
TV10-10F-XV		#10	
TV10-14F-XV		1/4"	



Vinyl Insulated Butt Splices

Cat. No.	Wire Range	Pkg Qty
TV18-BS-XV	22-18	15
TV14-BS-XV	16-14	15
TV10-BS-XV	12-10	15

Vinyl Insulated Butt Splices Set of connectors

Cat. No.	Wire Range	Qty	Pkg Qty
TV10-18-BS	22-18	5	15
	16-14	5	
	12-10	5	



Nylon Insulated Wire Joints

Cat. No.	Wire Range	Pkg Qty
TN18-WJ-XV	22-16	15
TN14-WJ-XV	16-14	15
TN10-WJ-XV	12-10	15



Vinyl Insulated Double Crimp Locking Fork

Cat. No.	Wire Range	Pkg Qty
TV18-10LFD-XV	22-16	15
TV18-6LFD-XV		
TV18-8LFD-XV		
TV14-10LFD-XV	16-14	15
TV14-6LFD-XV		
TV14-8LFD-XV		
TV10-10LFD-XV	12-10	15
TV10-6LFD-XV		
TV10-8LFD-XV		



Vinyl Insulated Locking Fork Terminal

Cat. No.	Wire Range	Pkg Qty
TV18-10LF-XV	22-16	15
TV18-6LF-XV		
TV18-8LF-XV		
TV14-10LF-XV	16-14	15
TV14-6LF-XV		
TV14-8LF-XV		
TV10-10LF-XV	12-10	15
TV10-6LF-XV		
TV10-8LF-XV		



Vinyl Insulated Female Disconnects – 250 Series

Cat. No.	Wire Range	Pkg Qty
TV18-250FD-XV	22-16	15
TV14-250FD-XV	16-14	15
TV10-250FD-XV	12-10	15



Vinyl Insulated male Disconnects – 250 Series

Cat. No.	Wire Range	Pkg Qty
TV18-250MD-XV	22-16	15
TV14-250MD-XV	16-14	15
TV10-250MD-XV	12-10	15



Vinyl Insulated Blade Terminal

Cat. No.	Wire Range	Pkg Qty
TV18-10BL-XV	22-16	15
TV14-10BL-XV		
TV14-18BL-XV		
TV10-10BL-XV	12-10	15



Vinyl Insulated Pin Terminal

Cat. No.	Wire Range	Pkg Qty
TV18-12PT-XV	22-16	15
TV14-12PT-XV	16-14	15
TV10-14PT-XV	12-10	15



Non insulated Ring Terminals

Cat. No.	Wire Range	Pkg Qty
T14-10R-XV	16-14	15
T14-8R-XV		
T10-10R-XV	12-10	15
T10-14R-XV		
T10-8R-XV		



Non insulated Fork Terminals

Cat. No.	Wire Range	Pkg Qty
T18-10F-XV	22-18	15
T18-8F-XV		
T14-10F-XV	16-14	15
T14-8F-XV		
T10-10F-XV	12-10	15
T10-14F-XV		
T10-8F-XV		



Vinyl Fully Insulated Double Crimp Female Disconnect

Cat. No.	Wire Range	Pkg Qty
TVF18-250FDD-XV	22-16	15
TVF14-250FDD-XV	16-14	15
TVF10-250FDD-XV	12-10	15



Vinyl Fully Insulated Female Disconnect

Cat. No.	Wire Range	Pkg Qty
TVF18-250FD-XV	22-16	15
TVF14-250FD-XV	16-14	15
TVF10-250FD-XV	12-10	15



Vinyl Insulated Piggy Back Disconnect

Cat. No.	Wire Range	Pkg Qty
TV18-250PD-XV	22-16	15
TV14-250PD-XV	16-14	15
TV10-250PD-XV	12-10	15



Vinyl Insulated Double Crimp Piggy Back Disconnect

Cat. No.	Wire Range	Pkg Qty
TV18-250PDD-XV	22-16	15
TV14-250PDD-XV	16-14	15
TV10-250PDD-XV	12-10	15

Catamount™

Terminals — Now in Convenient, Spillproof, Re-Usable Packaging!



Nylon Fully Insulated Female Disconnect

UL LISTED

Cat. No.	Wire Range	Pkg Qty
TNF18-250FD-XV	22-16	15
TNF14-250FD-XV	16-14	15
TNF10-250FD-XV	12-10	15

Nylon Fully Insulated Male Disconnect

UL LISTED

Cat. No.	Wire Range	Pkg Qty
TNF-18-250MD-XV	22-16	15
TNF-14-250MD-XV	16-14	15
TNF-10-250MD-XV	12-10	15

Vinyl Insulated Double Crimp Female Disconnect

UL LISTED

Cat. No.	Wire Range	Pkg Qty
TV18-250FDD-XV	22-16	15
TV14-250FDD-XV	16-14	15
TV10-250FDD-XV	12-10	15

Vinyl Insulated Double Crimp Male Disconnect

UL LISTED

Cat. No.	Wire Range	Pkg Qty
TV18-250MDD-XV	22-16	15
TV14-250MDD-XV	16-14	15
TV10-250MDD-XV	12-10	15

Vinyl Insulated Quick Splice

UL LISTED

Cat. No.	Wire Range	Pkg Qty
TV18-00QS-V	22-18	5
TV14-00QS-V	18-14	5
TV10-00QS-V	12-10	5

Nylon Fully Insulated Female Bullet

UL LISTED

Cat. No.	Wire Range	Pkg Qty
TNF18-4FB-XV	22-16	15
TNF14-4FB-XV	16-14	15

Nylon Fully Insulated Double Crimp Female Disconnect

UL LISTED

Cat. No.	Wire Range	Pkg Qty
TNF-18-250FDD-XV	22-16	15
TNF-14-250FDD-XV	16-14	15
TNF-10-250FDD-XV	12-10	15

Nylon Fully Insulated Double Crimp Male Disconnect

UL LISTED

Cat. No.	Wire Range	Pkg Qty
TNF-18-250MDD-XV	22-16	15
TNF-14-250MDD-XV	16-14	15
TNF-10-250MDD-XV	12-10	15

Nylon Fully Insulated Male Bullet

UL LISTED

Cat. No.	Wire Range	Pkg Qty
TNF18-4MB-XV	22-16	15
TNF14-4MB-XV	16-14	15

Catamount™ Terminal Tools



CM2000A

Cat. No.	Description
CM2000A	Crimping all Insulated Terminals 22-16 AWG (1.25 mm ²) 16-14 AWG (2 mm ²) 12-10 AWG (5.5 mm ²)
CM2000C	Crimping all single Crimp Insulated Female / Male Disconnect 22-16 AWG (1.25 mm ²) 16-14 AWG (2 mm ²) 12-10 AWG (5.5 mm ²)
CM2000D	Crimping Non-Insulated Terminals 22-16 AWG (1.25 mm ²) 16-14 AWG (2 mm ²) 12-10 AWG (5.5 mm ²) 8 AWG (8 mm ²)
CM2000G	Crimping Closed End Connectors & all Heat Shrinkable Terminals 22-16 AWG (1.25 mm ²) 16-14 AWG (2 mm ²) 12-10 AWG (5.5 mm ²)