

Power devices

1253



1252

Heavy duty grade power receptacles

Product description

2-pole, 3-wire grounding 50A, 125V/AC 50A, 250V/AC

Design features

- Heavy gauge galvanized steel mounting strap for corrosion resistance
- For use with copper or aluminum wire
- Flush receptacles fit one-gang or two-gang enclosures

Flush power receptacles (h) (f)



- Surface receptacles have patented lay-in terminals that accept up to #4 AWG wire
- Surface receptacle backs feature concentric knockouts and an adjustable cord clamp to allow wiring from back or bottom

Rating						
Α	V/AC	NEMA	Description	Color	Catalog no.	٤
50	125	5-50R	Flush mount power receptacle, matching plug A41	BK	□ 1253	• •
50	250	6-50R	Flush mount power receptacle, matching plug S42	BK	□ 1254	• •
1.1.1	1.11.4	00 (1) 1				

Listed to UL498, file no. E15058; CSA certified to CSA C22.2, no. 42

(h) 🚯 🎆 Surface power receptacles

Ra A	ting V/AC	NEMA	Description	Color	Catalog no.	
50	250	6-50R	Surface mount power receptacle, matching plug S42	BK	□ 1252	• •
Liste	ed to LIL 4	98 file no l	E15058: CSA certified to C22.2, no. 42: NOM certified			

Compatible wallplates / standard size for flush power receptacles	c 🖤 us		
Description	Color suffix	Catalog no.	
Thermoset 1-Gang wallplate for one power receptacle	A, B, V, W	□ 2068	• •
Thermoset 2-Gang wallplate for one power receptacle	A, B, LA, V, W	□ 2168	• •
Nylon 1-Gang wallplate for one power receptacle	V	□ 5068	• •
Polycarbonate 1-Gang wallplate of one power receptacle	B, BK, V, W	□ PJ724	•
Polycarbonate 2-Gang wallplate for one power receptacle	B, V, W	□ PJ703	•
Stainless steel 1-Gang wallplate for one power receptacle	Stainless Steel	□ 93221*	• •
Stainless steel 2-Gang wallplate for one power receptacle	Stainless Steel	93227*	• •

Listed to UL498, file no. E15058, *CSA certified to C22.2, no. 42

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), LA (Light Almond), V (Ivory), Stainless Steel, W (White)



Dimensional information: B-70 Specification information: Please visit www.eaton.com/wiringdevices Compliances, specifications and availability are subject to change without notice.

<u>a</u> Indicates NAFTA compliant - Page G-21 RoHS compliant - Page G-21