





Charging solutions for every device

Eaton's combination USB chargers offer consumers the ability to charge virtually any electronic device directly from a standard outlet without bulky adapters or powered computers. This innovative line quickly and conveniently charges smart phones, tablets, e-readers, cameras, MP3 players and more.

Perfect for use in residential, commercial and healthcare applications

- HomesL
- · Lounges and coffee houses
- · OEM applications

Offices
Airports

Hotels





USB charging devices

TR

Design features

Quick and easy access for both USB charging and electrical outlets

- 3.1A charging capacity on USB duplex receptacles
- USB devices available in single and duplex configurations
- USB devices available in 15A & 20A for multiple locations
- USB duplex receptacles available in hospital grade



USB charging station

Design features

Four USB charging ports rated at 5.0 Amps total for quick and convenient charging

- Charge up to 4 devices at the same time
- Replaces a standard receptacle

USB charging devices


Product description 1 1-2-pole, 3-wire grounding

15A, 125V/AC, 5V DC 700MA; 15A, 125V/AC, 5V DC 3.1A; 20A, 125V/AC, 5V DC 3.1A









· Tamper resistant receptacles provide compliance with 2014 NEC® Article 406.12 which states that all 15A and 20A, 125V/AC receptacles installed in dwelling units must be TR tamper resistant

· Automatic grounding system eliminates need for bonding jumper in grounded metal enclosure and provides redundant measure of ground continuity where jumper is used

- Thermoplastic top and back-body are virtually unbreakable to deliver years of durable performance
- Steel mounting strap is zinc plated for added corrosion resistance
- Convenient patented built-in wire strippers speeds installation
- Backwire clamps on side terminals provide for easy installation of #12 and #14 AWG wire (TR7740)
- Triple wipe blade contacts and double wipe ground contacts to insure long-term plug retention
- · Replaces a standard duplex receptacle



0.3/0

TR8355

TR7755







TR7740





7750

Combination USB charger with TR receptacle





Rating		USB rating				
Α	V/AC	Α	V/DC	Description	Color suffix	Catalog no.
15	125	3.1	5	USB charger with hospital grade TR duplex receptacle	GY, LA, RD, V, W	□ TR8255
20	125	3.1	5	USB charger with hospital grade TR duplex receptacle	GY, LA, RD, V, W	☐ TR8355
15	125	3.1	5	USB charger with TR duplex receptacle, wire leads	A, B, BK, GY, LA, V, W	☐ TR7755
20	125	3.1	5	USB charger with TR duplex receptacle, wire leads	A, B, BK, GY, LA, V, W	☐ TR7756
15	125	0.70	5	Combination USB charger with TR receptacle	A, BK, GY, LA, V, W	☐ TR7740
15	125	0.70	5	Combination USB charger With 1R receptacle	A, BK, GY, LA, V, VV	□ IN//4U

cULus Listed UL 498 and UL1310; NOM certified

USB charging station

Product description

5V/DC, 5.0A Total

Design features

- · USB charging ports rated at 5.0 Amps total (2.5A top two ports, 2.5A bottom two ports)
- Three (3) pre-stripped 6" wire leads for line, neutral and ground for quick and easy installation
- Automatic grounding system eliminates need for bonding jumper in grounded metal enclosure and provides redundant measure of ground continuity where jumper is used
- · Thermoplastic top and back-body are virtually unbreakable to deliver years of durable performance
- Steel mounting strap is zinc plated for added corrosion resistance
- Convenient patented built-in wire strippers speeds installation
- · Replaces a standard duplex receptacle

USB charging station

UL Listed to UL1310





A	V/DC	Description	Color suffix	Catalog no.
5.0	5	USB multiport charging station	BK, LA, V, W	□7750

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), RD (Red), V (Ivory), W (White).



Tamper resistant

Compliances, specifications and availability are subject to change without notice.

Visit our website: www.Arrowhart.com

Electrical Sector 203 Cooper Circle Peachtree City, GA 30269 United States Eaton.com Cooperwiringdevices.com

Electrical Sector Canada Operations 5925 McLaughlin Road Mississauga, Ontario, L5R 1B8 Canada EatonCanada.ca Cooperwiringdevices.com

Electrical Sector Mexico Operations Carr. Tlalnepantla Cuautitlán Km 17.8 s/n Col. Villa Jardín esq. Cerrada 8 de Mayo Cuautitlán, México CP 54800 México Eaton.mx Cooperwiringdevices.com

Eaton 1000 Eaton Boulevard Cleveland, OH 44122 United States Eaton.com

© 2015 Eaton All Rights Reserved Printed in USA Publication No. BR620005EN July 2015

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

