

**PLIERS**

**High Leverage Side-Cutting Pliers**



- High leverage pliers design and diamond-serrated jaws for optimum cutting and gripping performance.
- Forged from chrome vanadium steel for greater durability and strength.
- Precision-machined and induction-hardened blades strengthen cutters and provide consistent performance.
- Effectively cuts hardened wire, ACSR, bolts, screws and nails.
- Through-hardened steel for longer life.
- Exceeds ASME/ANSI specifications.
- Rugged riveted construction for smooth precise action.
- Stripping hole allows for easy and convenient wire stripping of #12 AWG wire (0151-09SM & 0151-09SD only).
- The wire looping hole perfectly forms wire for threaded connections (0151-09SM & 0151-09SD only).
- Lifetime limited warranty.
- Note: This is not an insulated tool.

**Molded Grip Only**

- Custom grip allows area for user identification.
- Slip-proof, ergonomic molded grips for increased comfort and reduced user fatigue.
- Wider grip design provides larger load bearing area.
- Location of handle ridge allows for user to “choke up” for greater control.

**Dipped Grip Only**

- Double layered vinyl handles for comfort and slip resistance.
- Handles allow for easy storage of tools in pouches and tool bags.



0151-09SM



0151-09M



0151-09D



0151-09SD



**MOLDED GRIP**

CAT. NO.	UPC NO.	DESCRIPTION
0151-09SM	89264 <b>N</b>	High Leverage Side-cutting Pliers W/Stripping Hole 9" molded grip
0151-08M	54701	High Leverage Side-cutting Pliers 8" molded grip
0151-09M	54702	High Leverage Side-cutting Pliers 9" molded grip
0151-09M-CP	95925	High Leverage Side-cutting Pliers 9" Counter Pack (Qty 5)

SPECIFICATIONS	8"	9"
Overall Length	8-1/2" (21.6 cm)	9-3/8" (23.8 cm)
Weight	.87 lbs. (.04 kg)	1.13 lbs. (.51 kg)

**DIPPED GRIP**

CAT. NO.	UPC NO.	DESCRIPTION
0151-09SD	89262 <b>N</b>	High Leverage Side-cutting Pliers W/Stripping Hole 9" dipped grip
0151-08D	89263 <b>N</b>	High Leverage Side-cutting Pliers 8" dipped grip
0151-09D	89250 <b>N</b>	High Leverage Side-cutting Pliers 9" dipped grip

SPECIFICATIONS	8"	9"
Overall Length	8-1/2" (21.6 cm)	9-3/8" (23.8 cm)
Weight	.87 lbs. (.04 kg)	1.13 lbs. (.51 kg)

International Tel: +1.815.397.7070  
Fax: +1.815.397.9247

Canada Tel: 800.435.0786  
Fax: 800.524.2853

USA Tel: 800.435.0786  
Fax: 800.451.2632