

## 9-In-1 Multi-Tool Driver



**NEW**



0153-43C

- Versatile multi-bit screwdriver, 9 tools in one.
- Drive hex nuts, Phillips, Square-recess and slotted fasteners.
- High-grade, rust resistant, chrome-plated finish.
- Precision machined, hardened steel bits.
- Soft, cushioned grip for extra comfort and torque.
- Lifetime limited warranty.
- Note: This is not an insulated tool.

CAT. NO.	UPC NO.	DESCRIPTION
0153-43C	13490	9-In-1 Multi-tool, Contains bits: #1 & #2 Phillips, #1 & #2 Square Recess and 3/16" & 1/4" Flat Tip Socket sizes included: 1/4", 5/16" & 3/8"
9953-15	10628 <b>R</b>	Replacement bits 9-In-1

### SPECIFICATIONS

<b>Length</b>	8" (203 mm)
<b>Weight</b>	.45 lbs. (.2 kg)
<b>Bit Sizes</b>	#1 & #2 Phillips, #1 & #2 Square Recess, 3/16" & 1/4" Flat Tip
<b>Socket Sizes</b>	1/4", 5/16" & 3/8"

## 6-In-1 Multi-Tool



0153-42C



- Versatile multi-bit screwdriver, 6 tools in one.
- Precision machined, hardened steel bits.
- High-grade, rust resistant, chrome-plated finish.
- Soft, cushioned grip for extra comfort and torque.
- Lifetime limited warranty.
- Note: This is not an insulated tool.

CAT. NO.	UPC NO.	DESCRIPTION
0353-41C	89218	6-In-1 Multi-tool, Contains: #1 & #2 Square Recess, 6mm Flat-Tip & #2 Phillips and 1/4" & 5/16" Hex.
0153-42C	56308	6-In-1 Multi-tool, Contains: 3/16" & 1/4" Flat-Tip, #1 & #2 Phillips and 5/16 & 1/4" Hex.
0153-42-CP	95933	6-In-1 Multi-tool Counter Pack (Qty 5)
9953-13	56310	Replacement bits – 3/16" & 1/4" Flat-tip and #1 & #2 Phillips
9953-14	89219	Replacement bits – #1 & #2 Square Recess and 6mm Flat Tip & #2 Phillips

### SPECIFICATIONS

<b>Length</b>	7-1/8" (20.6 cm)
<b>Weight</b>	.42 lbs. (.19 kg)
<b>Bit Sizes</b>	#1 & #2 Square Recess, 6mm Flat-tip, #2 Phillips and 5/16" & 1/4" Hex

Hand Tools

USA

Tel: 800.435.0786  
Fax: 800.451.2632

CANADA

Tel: 800.435.0786  
Fax: 800.524.2653

INTERNATIONAL

Tel: +1.815.397.7070  
Fax: +1.815.397.9247