


U.S. Electrical On-line Catalog





T&B Catalog Number: UPC Number: Description: ELL1-G 70450836988 1" x 90° Dark Gray 40 mil PVC Coated Hot-Dip Galvanized Rigid Steel Elbow.

Status:

Active

-T&B Product Line	087
Features	
-	A minimum .040" (40 mil) PVC coating on the exterior.
-	A nominal .002" (2 mil) blue urethane on the interior.
	Ocal-Blue standard radius elbows are factory bent to reduce the
-	Special radiuses and degrees are available upon request.
<u></u>	Color coded thread protectors on each end.
	Standard radiuses in 30°, 45°, 60° and 90&
General	
-Custom_Finish	sre_190
-Material	Steel
-Finish	Hot Dip Galvanized
-Color	Dark Gray
-Thread Protector Color	Blue
Dimension Information	
-Pipe Size (inches)	1
-Pipe Size (Metric Size Designator*)	27
-Degree of Bend	90
-Radius-R (inches)	5.75
-Radius-R (mm)	146.05
-Offset-C (inches)	8.63
-Offset-C (mm)	219.202
-Straight End-D (inches)	2.88
-Straight End-D (mm)	73.152
-Unbent Length (inches)	14.75
-Unbent Length (mm)	374.65
Technical Information	
-Chemical Resistance Chart	Available on Website
Specifications	
-Ocal Specification Guide-1995 Master F	or Avvailł&De on Website
-Ocal Specification Guide-1995 Master F	onAvvanilaboon Website
-Ocal Specification Guide-2004 Master F	or Avvailł&De on Website
-Ocal Specification Guide-2004 Master F	on/waaiilab@eCon Website
Packaging	
-Package in Units	20
-T&B Sold in UOM	Each
-T&B Weight Per UOM	2.1 lbs. Each
Application Support	
-T&B Sales Drawings	wsd-000551
-Recommended Installation Procedures	Available on Website
-NEMA Standards-RN 1	Available on Website



U.S. Electrical On-line Catalog

-NEC Table 8		Available on Website	
Notes			
-*Note		Metric size designator (ANSI C80. 1-1994)	
-**Note		Dimensional values are of un-coated elbows.	
-***Note		Standard color is dark gray. Also available in white ar	nd light blue.
Certificatio	ons		
-RoHS Compli	iance	No	
Certificatio	ons		
(h)	()		



File Nbr:

E 46453

For further technical assistance, please contact us...

T&B Technical Support MS 3B-50 8155 T&B Blvd. Memphis, TN 38125

Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@tnb.com

Thomas & Betts - USA 8155 T&B Blvd. Memphis, TN 38125 www.tnb.com