



## Features

- Operates on programmed start electronic ballast except where otherwise identified
- Energy savings and reduced maintenance cost
- TCLP compliant\*
- High colour consistency

## Applications

- Hotels
  - Schools
  - Ambient lighting
  - Retail stores
  - Hospitals
  - Offices
- (Living room, kitchen, under cabinet lighting)



Dia. = 5/8 in. (16 mm)

## T5 Preheat Start

Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Average life (hrs)	Initial lumens (lm)	Mean lumens (lm)	Nominal length (in.) (mm)	Efficacy (lm/W)	Case qty
56509	F4T5/CW/PH/G5/ELUME	4	Min Bipin	4100	62	6000	120	112	6 152	30	48
56510	F6T5/CW/PH/G5/ELUME	6	Min Bipin	4100	62	7500	240	225	9 229	40	48
56511	F6T5/DL/PH/G5/ELUME	6	Min Bipin	6500	62	7500	210	197	9 229	35	48
56512	F8T5/CW/PH/G5/ELUME	8	Min Bipin	4100	62	7500	350	329	12 305	44	48
56513	F8T5/DL/PH/G5/ELUME	8	Min Bipin	6500	62	7500	310	291	12 305	39	48
56518	F13T5/WW/PH/G5/ELUME	13	Min Bipin	3000	62	7500	800	752	21 530	62	48
57392	F13T5/CW/PH/G5/ELUME	13	Min Bipin	4100	62	7500	740	695	21 530	57	48

## T5 Program Start

\* Based on a 3 hour start \*\* Based on a 12 hour start

Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Rated life PS/PRS bal-last 3-12 hrs	Initial lumens (lm)	Mean lumens (lm)	Nominal length (in.) (mm)	Efficacy (lm/W)	Case qty
59187*	F14T5/35K/8/PS/G5/ELUME	14	Min Bipin	3500	85	24 000* 30 000**	1350	1280	22 559	96	25
59188*	F14T5/41K/8/PS/G5/ELUME	14	Min Bipin	4100	85	24 000* 30 000**	1350	1280	22 559	96	25
59189*	F14T5/50K/8/PS/G5/ELUME	14	Min Bipin	5000	85	24 000* 30 000**	1300	1230	22 559	93	25
59190*	F21T5/35K/8/PS/G5/ELUME	21	Min Bipin	3500	85	24 000* 30 000**	2100	2000	34 864	100	25
59191*	F21T5/41K/8/PS/G5/ELUME	21	Min Bipin	4100	85	24 000* 30 000**	2100	2000	34 864	100	25
59192*	F21T5/50K/8/PS/G5/ELUME	21	Min Bipin	5000	85	24 000* 30 000**	2100	2000	34 864	100	25
59196*	F28T5/35K/8/PS/G5/ELUME	28	Min Bipin	3500	85	24 000* 30 000**	2900	2750	46 1168	104	25
59197*	F28T5/41K/8/PS/G5/ELUME	28	Min Bipin	4100	85	24 000* 30 000**	2900	2750	46 1168	104	25
59198*	F28T5/50K/8/PS/G5/ELUME	28	Min Bipin	5000	85	24 000* 30 000**	2750	2610	46 1168	98	25