




Order code	Description	Base	Volts (V)	Watts (W)
38139	HORIZONTAL BOTTOM SCREW MOUNT	2G11	600	75
38221	HORIZONTAL SNAP-IN MNT	2G11	600	75
38222	HORIZ 90D BOTTOM SNAP-IN MNT	2G11	600	75
38143	13W HORIZ. 2 HOLE SCREW MOUNT	2GX7	600	75
38110	9 WT VERTICAL MOUNT SNAP-IN	G23	600	75
38108	7-9WT VERT MNT 4 HOLE METAL/CLIP	G23 / G23-2	600	75
38214	5-9W HORIZ.MOUNT 2 HOLE G23-2	G23 / G23-2	600	75
11588	CF13-HSM HORIZ BOTTOM SCREW MT	G23 / GX23	600	75
38115	13 WT VERTICAL 4 HOLE SCR MNT	G24d-1	600	75
38120	13W/TTT HORIZONTAL SCREW MOUN	G24d-1	600	75
38123	18WT 4-PIN VERT 4 HOLE SRW MN	G24d-1	600	75
38127	18WT 4-PIN HORIZONTAL SCR MNT	G24d-1	600	75
38122	18WT VERTICAL 4 HOLE SCREW MN	G24d-2	600	75
38126	18WT HORIZONTAL SCREW MOUNT	G24d-2	600	75
11633	26WT VERT TOP/BOTTOM SCR MNT	G24d-3	600	75



Order code	Description	Base	Volts (V)	Watts (W)
38132	26WT VERTICAL 4 HOLE SCREW MN	G24d-3	600	75
38135	26WT HORIZONTAL SCREW MOUNT	G24d-3	600	75
38116	13 WT 4-PIN VERT 4HL SCR MNT	G24q-1	600	75
38121	13WT 4-PIN HORZ SCR MNT 2 HOL	G24q-1	600	75
38064	SKT42 13-42W 4PIN UNIV.SOCKET	G24q-1/G24q-2 /G24q-3 /G24q-4	600	75
38218	18WT VERT TOP/BOTTOM SCR MNT	G24q-2	600	75
38113	13 WT VERTICAL MOUNT SNAP-IN	GX23	600	75
38112	13 WT VERTICAL MOUNT 4 HOLE	GX23 / GX23-2	600	75
38119	CF13-HSI HORZ BOTTOM SNAPIN MT	GX23 / GX23-2	600	75
38133	26WT 4-PIN VERT 4 HOLE SCR MN	GX24q-3	600	75
38136	26WT 4-PIN HORIZONTAL SCREW M	GX24q-3	600	75