


Cable-to-Cable or Cable-to-Rod Connectors

One-piece construction for cable-to-cable, cable-to-rod, "T" and "X" connections

- Suitable for direct burial or in concrete
- Replaces exothermic welds
- Made from high-conductivity wrought copper



Cat. No.	Cable to Cable Range						Rod to Cable range								
	Main	Die Code	TBM14 and 15 Die Cat. No.	Branch	Die Code	TBM14 and 15 Die Cat. No.	Ground Rod (in.)	Die Code	TBM14 and 15 Die Cat. No.	Cable	Die Code	TBM14 and 15 Die Cat. No.			
GG21-21	#2 or #1	45	15526 [2]	#2 or #1	45	15526 [2]	-	-	-	-	-	-			
GG10-10	1/0	54	15511 [2]	1/0	54	15511 [2]									
GG2030-21	2/0 or 3/0	60	15532 [2]	#2 or #1	50-45	15526 [2] 15530 [2]									
GG2030-10				1/0	54H	15511 [2]									
GG2030-2030				2/0-3/0	60	15532 [2]									
GG40250-21	4/0 or 250 kcmil	71H	15514-CK [2]	#2	45 50	15526 [2] 15530 [2]	1/2 5/8	71 80H	15514-CK 15517	#2 or #1	45 50	15526 15530			
GG40250-10				1/0 kcmil	54H	15511 [2]				1/0	54	15511			
GG40250-2030				2/0 or 3/0	60	15532-CK [2]				2/0 or 3/0	60	15532 15532			
GG40250-40250				4/0 or 250 kcmil	71H	15514-CK [2]				4/0 or 250 kcmil	71H	15514-CK [2]	4/0 or 250 4/0 or 250 4/0 or 250	71H 71H 71H	15514-CK 15514-CK
GG500-40250	500 kcmil	87H	15506 [2]	4/0 or 250 kcmil	71H	15514-CK [2]	3/4 5/8	87H	15506	500	87H	15506			
GG500-500				500 kcmil	87H	15506 [2]				500	87H				
GG500-350				350 kcmil	80H	15606 [2]				350 kcmil	80H	15606 [2]	350	80H	
GG500-2030				2/0 or 3/0	60	15532-CK [2]				2/0 or 3/0	60	15532-CK [2]	-	-	2/0 or 3/0
GG350-350	350 kcmil	80H		350 kcmil	80H	15606 [2]	-	-	-	-	-	-			

Uses 15500TB adaptor for 15-Ton Tools.
Optional ground rod knurling die or TBM14 and 15 tools: 15508.
Optional ground rod knurling tool: 240-31565-94.

[2] Number of crimps.