



Steel Stud Boxes

Device Boxes




CI3102-LSSAX




CI3102-SSX




CI1204-3/4-SSX-HV




CI2104-LSSAX




CI2104-LSSA-2X




CI2104-LSSX




CI2104-LSS1X-1




CI2104-LSS2X-1



CI2104-LSS3X-1



CI2104-LSS-2X



CI2104-LSS-3X



CISSX-6




Cat. No.	Volume (Cu. in.)	Width (in.)	Features	Knockouts			Pryouts
			Clamps	1/2 in. ends	1/2 in. bottom	3/4 in. ends	ends
Device Boxes — 2 in. Deep — Gangable — 3 in. High							
CI3102-LSSAX	12.0	2	loomex/BX	-	-	-	4
CI3102-SSX	12.0	2	-	2	-	-	-
Device Boxes — 2-1/2 in. Deep — Pre-Ganged — 3 in. High							
CI1204-3/4-SSX-HV	16.0	2	-	-	-	2	-
CI2104-LSSAX	12.5	2	loomex/BX	-	-	-	4
CI2104-LSSA-2X	25.0	3-3/4	loomex/BX	-	-	-	8
CI2104-LSSA-3X	37.5	5-1/2	loomex/BX	-	-	-	12
CI2104-LSSX	12.5	2	loomex/BX	-	-	-	4
CI2104-LSS1X-1	12.5	2	loomex/BX	-	-	-	4
CI2104-LSS2X-1	25.0	3-3/4	loomex/BX	-	-	-	8
CI2104-LSS3X-1	37.5	5-1/2	loomex/BX	-	-	-	12
CI2104-LSS2X	25.0	3-3/4	loomex/BX	-	-	-	8
CI2104-LSS3X	37.5	5-1/2	loomex/BX	-	-	-	12


Cat. No.	Description
Support Brackets	
CISSX-6	Support bracket extension for 6 in. metal stud

Steel Stud Boxes


Device Boxes




CI3104-KSSX




BC3104-KSS1X-1




BC3104-LSSAX




BC3104-LSSX




CI3104-LSS1X-1




CI3104-LSSA1X-1



CI1504-LSSAX



CI3004-LSSAX-1



CI3004-LSSX-1



CISSX-6



Cat. No.	Volume (Cu. in.)	Features	Knockouts			Pryouts
		Clamps	1/2 in. ends	1/2 in. bottom	3/4 in. ends	ends
Device Boxes — 2-1/2 in. Deep — Gangable — 3 in. x 2 in.						
CI3104-KSSX	16.0	-	2	2	2	-
BC3104-KSS1X-1	16.0	-	2	2	2	-
BC3104-LSSAX	16.0	loomex/BX	-	-	-	4
BC3104-LSSX	16.0	loomex/BX	-	-	-	4
CI3104-LSS1X-1	16.0	loomex/BX	-	-	-	4
CI3104-LSSA1X-1	16.0	loomex/BX	-	-	-	4
CI3104-SSX	16.0	loomex/BX	2	2	-	-
Device Boxes — 2-1/2 in. Deep — Non-Gangable — 3 in. x 2 in.						
CI1504-LSSAX	15.0	loomex/BX	-	-	-	4
Device Boxes — 3 in. Deep — Gangable — 3 in. x 2 in.						
CI3004-LSSAX-1	18.0	loomex/BX	-	-	-	4
CI3004-LSSX	18.0	loomex/BX	-	-	-	4
CI3004-LSSX-1	18.0	loomex/BX	-	-	-	4


Cat. No.	Description
Support Brackets	
CISSX-6	Support bracket extension for 6 in. metal stud

Steel Stud Boxes


347 Volt Boxes and Power Communication Boxes




CI1204-3/4-SSX-HV




CI1204-LSSAX-HV




CI4204-KSSX




CI4204-LSSX




CI4204-LSSAX




CI4304-LSSX



CI4304-LSSAX



CI1204-SSX-HV



CI1204-SS1X-HV



CISSX-6



Cat. No.	Volume (Cu. in.)	Features	Knockouts			Pryouts
		Clamps	1/2 in. ends	1/2 in. bottom	3/4 in. ends	ends
347 Volt Boxes — 2-1/2 in. Deep — Gangable — 3 in. x 2-1/4 in.						
CI1204-SSX-HV	16.0	loomex/BX	2	-	-	-
CI1204-3/4-SSX-HV	16.0	loomex/BX	-	-	2	-
CI1204-LSSAX-HV	16.0	loomex/BX	-	-	-	4
CI1204-SS1X-HV	16.0	loomex/BX	2	-	-	-
Power / Communication Boxes — 2-1/2 in. Deep — Pre-Ganged — 3 in. x 2 in. / gang						
CI4204-KSSX	12.5 / gang	-	4	4	4	-
CI4204-LSSX	12.5 / gang	loomex/BX	2	2	2	4
CI4204-LSSAX	12.5 / gang	loomex/BX	2	2	2	4
CI4204-LSSAX-1	12.5 / gang	loomex/BX	2	2	2	4
CI4304-LSSX	12.5 / gang	loomex/BX	-	-	-	4
CI4304-LSSAX	12.5 / gang	loomex/BX	-	-	-	4

Cat. No.	Description
Support Brackets	
CISSX-6	Support bracket extension for 6 in. metal stud

Steel Stud Boxes

4 in. and 4-11/16 in. Square Boxes and 4 in. Octagonal Boxes



BC52151-KSSX



BC52171-KSSX



CI52171-KSSX-1




CI52171-1-SSX-1



CI72171-KSSX



CI54151-KSSX



BC54151-LSSAX



BC1110-SSX



CI54171-KSSX



BC52171-KSSXHVKIT



Cat. No.	Volume (Cu. in.)	Features		Knockouts					Pryouts sides
		Clamps	Raised Ground Screw	1/2 in. sides	1/2 in. bottom	3/4 in. sides	3/4 in. bottom	1 in. sides	
4 in. Square Boxes – 1-1/2 in. Deep									
BC52151-KSSX	21.0	-	yes	7	4	3	2	-	-
4 in. Square Boxes – 2-1/8 in. Deep									
BC52171-KSSX	30.0	-	yes	7	4	3	2	-	-
CI52171-KSSX-1	30.0	-	yes	7	4	3	2	-	-
CI52171-1-SSX-1	30.0	-	yes	-	4	-	2	2	-
4-11/16 in. Square Boxes – 2-1/8 in. Deep									
CI72171-KSSX	42.0	-	yes	8	4	4	2	-	-
4 in. Octagonal Boxes – 1-1/2 in. Deep									
CI54151-KSSX	15.0	-	yes	2	4	2	2	-	-
BC54151-LSSAX	15.0	loomex/BX	-	-	1	-	-	-	4
4 in. Octagonal Boxes – 2-1/8 in. Deep									
CI54171-KSSX	21.0	-	yes	2	4	2	2	-	-
4 in. Square – 2-1/8 in. Deep									
BC52171-KSSXHVKIT	33.6	"SSX"	yes	6	-	2	-	-	-

Cat. No.	Volume (Cu. in.)	Features		Knockouts		
		Brackets	Raised Ground Screw	1/2 in. ends	1/2 in. bottom	1/2 in. sides
4 in. Square Boxes – 1-1/2 in. Deep						
BC1110-SSX	16.5	"SSX"	yes	7	4	3