

Assorted Die Kits

EZ-CK SS DIEKIT — Die sets Kit

All the Thomas & Betts dies you need to crimp the complete T&B E-Z-Ground® connector offering, presented in a two sided metal carrying case. The reverse side of this kit allows you to keep all your colour coded Blackburn® crimping dies in one convenient location. A cable vs die reference chart inside each cover lets you sort and organize all your Blackburn® compression connector dies for either copper or aluminum conductors. Additional compartments for cutting dies and adaptors round off this great package.

Cat. No.	Die Cat. No.	Qty.	Die Colour	Copper	Aluminum
EZ-CK SS DIEKIT	15528SS	—	Brown	2 AWG	—
	15513SS		Green	1 AWG	4 AWG
	15508SS		Pink	1/0 AWG	2 AWG
	15526SS		Black	2/0 AWG	1 AWG (Gold)
	15530SS		Orange	3/0 AWG	1/0 AWG (Tan)
	15511SS		Purple	4/0 AWG	2/0 AWG (Olive)
	15510SS		Yellow	250 kcmil	—
	15534SS		White	300 kcmil	4/0 AWG
	15514SS		Red	350 kcmil	250 kcmil
	15506SS		Brown	500 kcmil	350 kcmil
	15515SS		Black	750 kcmil	650 kcmil
	15G121R		—	—	—
	15G86R	—	—	—	—
	15501A				
	15G126R				
	CTB8				
	COLCHA2-E				
	GRNDIESEL-E				



Side A



Side B



Assorted Die Kits

OD-T00L-KIT

This kit is offered in a metal carrying case with heavy duty handle and sturdy closures. The best way to carry the connectors and tools you need for commercial and residential hook-ups.




Cat. No.	Kit includes	Qty.
OD-T00L-KIT	Metallic carrying case	1
	ODB1 – Blackburn® Compression Tool	
	WR159 – Compression connectors	18
	WR189 – Compression connectors	12
	WR289 – Compression connectors	5
	WR379 – Compression connectors	
	WR419 – Compression connectors	
	C5C – Insulating covers	30
	C7C – Insulating covers	15

ODB Compression tool with straight wooden handles and ODH1 insulated heat cover (Installed on ODB1) can be ordered separately.

Assorted Die Kits

TBM45SKIT-N includes the following:

Cat. No.	Qty.	Cat. No.	Cable Size	Items	Weight/lb. each
TBM45SKIT-N	25	54130	#8	One Hole Lugs	20
		54105	#6		
		54106	#4		
		54107	#2-#3		
		54108	#1		
		54143-TB	#2	2-Way Connectors	
		54136	#6		
		54804	#8		
		54805	#6		
		54806	#4		
		54807	#2-#3		
		54808	#1		
	1	TBM45S Tool	—	—	



Assorted Die Kits



Cat. No.	Description
PWK1	Empty case – includes Color-Keyed® wall chart; make up your own selection of Color-Keyed® lugs, splices, taps or motor disconnects
PWK4	Metal cabinet that holds four of the PWK1 shells slide out for easy removal of PWK1
MDPWK12	Selection of size 1 and 2 male motor disconnects plus insulators; to connect 60 single line to single line load motor leads, #12 AWG through #2 AWG; tools not included
MDPWK23	Selection of size 2 and 3 male motor disconnects plus insulators; to connect 54 single line to single line load motor leads, #12 AWG through 4/0 AWG; tools not included
MDKITL	Includes Tool

Carrying Cases

Case Contents MDPWK12				
1 PWK1	10 MD1210F-1	6 MD8M-2	6 MD8F-2	30 BOOT-1
10 MD1210M-1	10 MD8F-1	6 MD6M-2	6 MD6F-2	6 MD1210M-2
10 MD8M-1	10 MD6F-1	6 MD4M-2	6 MD4F-2	6 MD1210F-2
10 MD6M-1	30 MDBOOT-2	6 MD2M-2	6 MD2F-2	—
Case Contents MDPWK23				
1 PWK1	6 MD1210F-2	3 MD2M-3	3 MD2F-3	6 MD1M-2
6 MD1210M-2	6 MD8F-2	3 MD1M-3	3 MD1F-3	36 MDBOOT-2
6 MD8M-1	6 MD6F-2	3 MD10M-3	3 MD10F-3	18 MDBOOT-3
6 MD6M-1	6 MD4F-2	3 MD20M-3	3 MD20F-3	—
6 MD4M-1	6 MD2F-2	3 MD30M-3	3 MD30F-3	
6 MD2M-1	6 MD1F-2	3 MD40M-3	3 MD40F-3	
Case Contents MDKITL				
1 PWK1	1 TBM45S	24 MDBOOT-2	3 M2D2M-2	6 MD8M-1
3 M2D4M-2	3 M2D6M-2	3 M2D8M-2	12 M2DBOOT-2	6 MD8F-1
12 MDBOOT-1	12 MD2F-2	12 MD4F-2	12 MD6F-2	6 MD8M-2
12 M2D8M-2	6 MD2M-2	6 MD4M-2	6 MD6M-2	6 MD6M-2
6 MD6F-1	—	—	—	—