

Tak-Ty® Hook & Loop Cable Tie Mounts

- For use with TTS Tak-Tape™ and HLT/HLS Tak-Ty® Hook & Loop Cable Ties
- Unique cradle design provides maximum stability for cable bundle
- For indoor use only
- Dimensions: 1.10"L x 1.10"W x .34"H (27.9mm x 27.9mm x 8.6mm)



Part Number	Material	Color	Mounting Method	Std. Pkg. Qty.	Std. Ctn. Qty.
ABMT-A-C*	Nylon 6.6	Natural	Rubber	100	1000
ABMT-A-C20*		Black		100	1000
ABMT-S6-C	Nylon 6.6	Natural	#6 (M3) Screw	100	1000
ABMT-S6-C20		Black		100	1000
ABMT-S6-C60**	Flame Retardant Nylon 6.6	Black		100	1000
ABMT-S6-C69**		Natural		100	1000

*Maximum static load for adhesive backed mounts is .38 lbs. (174g).

**Flame retardant products are manufactured from a material that is rated UL 94V-0.

4-Way Adhesive Backed Cable Tie Mounts

- Allow cable tie entry from all four sides
- Available in multiple sizes to match application load requirements
- Produced 2-up and with tear tabs for fast and easy liner removal to speed installation
- Rubber-based adhesive provides a strong and reliable bond
- For indoor use only



Part Number	Used With Cable Ties	Length		Width		Material	Color	Std. Pkg. Qty.	Std. Ctn. Qty.
		In.	mm	In.	mm				
ABM1M-A-C	M	.50	12.7	.50	12.7	Nylon 6.6	White	100	500
ABMM-A-C	M, I	.75	19.1	.75	19.1	ABS	White	100	500
ABMM-A-C20	M, I	.75	19.1	.75	19.1		Black	100	500
ABM2S-A-C	M, I, S	1.00	25.4	1.00	25.4		White	100	500
ABM2S-A-C14	M, I, S	1.00	25.4	1.00	25.4		Gray	100	500
ABM2S-A-C15	M, I, S	1.00	25.4	1.00	25.4		Ivory	100	500
ABM2S-A-C20	M, I, S	1.00	25.4	1.00	25.4		Black	100	500
ABM100-A-C	M, I, S	1.00	25.4	1.00	25.4	Nylon 6.6	White	100	1000
ABM100-A-C15	M, I, S	1.00	25.4	1.00	25.4		Ivory	100	1000
ABM100-A-D20	M, I, S	1.00	25.4	1.00	25.4		Black	500	5000
ABM112-A-C	M, I, S	1.12	28.6	1.12	28.6		White	100	500
ABM112-A-D20	M, I, S	1.12	28.6	1.12	28.6		Black	500	5000
ABM3H-A-L	M, I, S, HS, LH, H, HLM	1.50	38.1	1.50	38.1		White	50	500
ABM3H-A-L20		1.50	38.1	1.50	38.1		Black	50	500
ABM4H-A-L		2.00	50.8	2.00	50.8		White	50	500

Cable Tie Cross Sections: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, H = Heavy, HLM = Miniature Tak-Ty® Hook & Loop Cable Ties.