

**Long Barrel Copper Lug**  
**T&B Catalog Number:**

54965BE

**UPC Number:**


78621089828

**Status:**

Active

**Description:**

Copper One-Hole Lug - Straight Long Barrel - max 35KV, 3/0 AWG Wire, 1/2" Bolt Size, Tin Plated Blind End, Orange 50



**General**

|                 |            |
|-----------------|------------|
| Material        | Copper     |
| Finish          | Tin Plated |
| Wire Size       | 3/0 AWG    |
| Number of Studs | 1          |
| Stud Size       | 1/2        |
| Tongue Angle    | Straight   |
| Barrel Length   | Long       |
| Barrel Shape    | Standard   |
| Tongue Width    | Standard   |
| Peep Hole       | N          |
| Marking         | Standard   |
| Hole Shape      | Round      |
| Die Color       | Orange     |
| Die Code        | 50         |

**Dimension Information**

|            |       |
|------------|-------|
| A (inches) | 2.703 |
| B (inches) | 1.25  |
| C (inches) | .922  |
| D (inches) | .125  |
| E (inches) | .625  |
| F (inches) | .5    |

**Specifications**

|                |              |
|----------------|--------------|
| Voltage Rating | 600V to 35KV |
|----------------|--------------|

**Tooling**

|                           |                      |
|---------------------------|----------------------|
| Connector & Tooling Chart | Available on Website |
|---------------------------|----------------------|

**Packaging**

|                    |                    |
|--------------------|--------------------|
| T&B Order Multiple | 10                 |
| T&B Inner Pack     | 10                 |
| Package in Units   | 100                |
| T&B Sold in UOM    | Each               |
| T&B Weight Per UOM | 10.19 lbs. per 100 |

**Application Support**

|                        |                      |
|------------------------|----------------------|
| T&B Instruction Sheets | ta01025-tb2          |
| Overview               | Available on Website |

**Notes**

Dimensions given for reference only. Dimensions may vary up to .030.

**Certifications**

|                 |     |
|-----------------|-----|
| RoHS Compliance | Yes |
|-----------------|-----|

## Certifications



File Nbr:  
E9809

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)