















4" LOW VOLTAGE TRIM SERIES ADJUSTABLES

Project: _____

Fixture Type: _____

Location: _____

Contact/Phone: _____

Trim Series	Dimensions	Aperture	Catalog No.	Housing/Lamp Compatibility
 Baffle Downlight/ Adjustable	 5"	3 3/8"	444W-WH - White Baffle, White Trim 444B-WH - Black Baffle, White Trim 444B-BL - Black Baffle, Black Trim 444B-ABZ - Black Baffle, Classic Aged Bronze Trim 444B-SC - Black Baffle, Satin Chrome Trim	IC44N/IC44W/IC44S/TC44/TC44V/TC44S/TC44R: 50W MR16, TC47/TC47V: 75W MR16 APT44: 50W MR16
 Cone Downlight/ Adjustable	 5"	3 3/8"	447B-WH - Black Alzak®, White Trim 447C-WH - Clear Alzak®, White Trim 447G-WH - Gold Alzak®, White Trim 447HZ-WH - Haze, White Trim 447PT-SC - Pewter Alzak®, Satin Chrome Trim 447WHZ-ABZ - Wheat Haze, Classic Aged Bronze Trim 447WHZ-WH - Wheat Haze, White Trim	IC44N/IC44W/IC44S/TC44/TC44V/TC44S/TC44R: 50W MR16, TC47/TC47V: 75W MR16 APT44: 50W MR16
 Flush Gimbal Ring	 5"		440-ABZ - Classic Aged Bronze Trim 440-BL - Black Trim 440-SC - Satin Chrome Trim 440-WH - White Trim	IC44N/IC44W/IC44S/TC44/TC44V/TC44S/TC44R: 50W MR16, TC47/TC47V: 75W MR16 APT44: 50W MR16
 Adjustable Slot Aperture	 5"	1 1/2" x 2 1/8" Oblong	445-WH - White Trim	IC44N/IC44W/IC44S/TC44/TC44V/TC44S/TC44R: 50W MR16, TC47/TC47V: 75W MR16 APT44: 50W MR16
 Eyeball with Black Baffle	 5"		448-SC - Satin Chrome Trim 448-WH - White Trim	IC44N/IC44W/IC44S/TC44/TC44V/TC44S/TC44R: 50W MR16, TC47/TC47V: 75W MR16 APT44: 50W MR16
 Aiming Elbow	 4 7/8"		449-ABZ - Classic Aged Bronze Trim 449-BL - Black Trim 449-SC - Satin Chrome Trim 449-WH - White Trim	IC44N/IC44W/IC44S/TC44/TC44V/TC44S/TC44R: 50W MR16, TC47/TC47V: 75W MR16 APT44: 50W MR16







4" LOW VOLTAGE TRIM SERIES ADJUSTABLES

Project: _____

Fixture Type: _____

Location: _____

Contact/Phone: _____

Trim Series	Dimensions	Aperture	Catalog No.	Housing/Lamp Compatibility
 AVIO™ Square Gimbal Ring	 7 3/8"		XR16101BL - Black Trim XR16101GP - Graphite Trim XR16101SL - Silver Trim XR16101WH - White Trim	IC44N/IC44W/IC44S/TC44/TC44V/TC44S/TC44R: 50W MR16, TC47/TC47V: 75W MR16
	Adjustment: 45° Vertical			

