

5000
Series




18.8 STAINLESS STEEL FASTENERS ATTACHES ACIER INOXYDABLE 18.8

Corrosion resistant Type 300 Series (18% chromium - 8% nickel). Used in Marine applications, food processing equipment and wherever resistance to most acids and chemicals is required. Non-magnetic. UNC thread.

Order by Stock Number



18.8 HEX CAP SCREWS and NUTS



	Dia.	1/4-20	Std. Pkg.	5/16-18	Std. Pkg.	3/8-16	Std. Pkg.	1/2-13	Std. Pkg.
Length	3/4	5000-307	100	5000-442	100	5000-487	100	—	—
	1	5000-309	100	5000-444	100	5000-489	100	5000-579	25
	1-1/2	5000-313	100	5000-448	100	5000-493	100	5000-583	25
	2	5000-316	100	5000-451	100	5000-496	100	5000-586	20
	2-1/2	5000-318	50	5000-453	50	5000-498	50	5000-588	20
3	5000-320	25	5000-455	25	5000-500	25	5000-590	10	
Hex Nuts		5026-014	100	5026-016	100	5026-018	100	5026-022	50



18.8 FLAT WASHERS

Standard Package 100 Pcs., *50 Pcs.

Stock No.	Bolt Size	I.D.	O.D.	Thick.
5055-206	#6	.147	3/8	.031
5055-208	#8	.172	3/8	.031
5055-210	#10	.200	7/16	.037
5055-214	1/4	.265	11/16	.050
5055-216	5/16	11/32	3/4	.050
5055-218	3/8	25/64	7/8	.062
5055-222*	1/2	9/16	1-1/4	.078



18.8 REGULAR LOCK WASHERS

Std. Package 100 Pcs.

Stock No.	Bolt Size
5058-014	1/4
5058-016	5/16
5058-018	3/8
5058-022	1/2



18.8 FINISHING WASHERS


Std. Package 100 Pcs.

Stock No.	Screw Size
5056-971	#6
5056-973	#8
5056-975	#10
5056-979	1/4




18.8 NYLON INSERT LOCK NUTS

Stock No.	Bolt Size	Std. Pkg.
5034-006	6-32	100
5034-008	8-32	100
5034-010	10-24	100
5034-011	10-32	100
5034-014	1/4-20	100
5034-016	5/16-18	100
5034-018	3/8-16	100
5034-022	1/2-13	50




18.8 FENDER WASHERS

Stock No.	Bolt Size	Outside Diameter	Std. Pkg.
5057-394	No. 10	1"	100
5057-395	1/4	1-1/4	100
5057-396	5/16	1-1/2	100
5057-398	3/8	1-1/2	100
5057-400	1/2	2"	50



18.8 STAINLESS COTTER PINS

Stock No.	Size	Std. Pkg.
5080-091	3/32 x 1	100
5080-095	3/32 x 1-1/2	100
5080-141	1/8 x 1	100
5080-145	1/8 x 1-1/2	100
5080-148	1/8 x 2	100
5080-171	5/32 x 1-1/2	100
5080-174	5/32 x 2	100



18.8 STAINLESS CARRIAGE BOLTS

Stock No.	Size	Std. Pkg.
5002-309	1/4 x 1	100
5002-313	1/4 x 1-1/2	100
5002-316	1/4 x 2	100
5002-318	1/4 x 2-1/2	50
5002-320	1/4 x 3	50
5002-444	5/16 x 1	50
5002-448	5/16 x 1-1/2	50
5002-451	5/16 x 2	50
5002-453	5/16 x 2-1/2	25
5002-455	5/16 x 3	25
5002-489	3/8 x 1	50
5002-493	3/8 x 1-1/2	50
5002-496	3/8 x 2	25
5002-498	3/8 x 2-1/2	25
5002-500	3/8 x 3	25
5002-504	3/8 x 4	10



18.8 STAINLESS LAG BOLTS

Stock No.	Size	Std. Pkg.
5003-309	1/4 x 1	50
5003-313	1/4 x 1-1/2	50
5003-316	1/4 x 2	50
5003-318	1/4 x 2-1/2	25
5003-320	1/4 x 3	25
5003-448	5/16 x 1-1/2	50
5003-451	5/16 x 2	50
5003-453	5/16 x 2-1/2	25
5003-455	5/16 x 3	25
5003-493	3/8 x 1-1/2	50
5003-496	3/8 x 2	50
5003-498	3/8 x 2-1/2	25
5003-500	3/8 x 3	25
5003-504	3/8 x 4	20
5003-586	1/2 x 2	50
5003-590	1/2 x 3	25
5003-594	1/2 x 4	20



18.8 STAINLESS SOCKET CAP SCREWS

Stock No.	Size	Std. Pkg.
5007-309	1/4 x 1	100
5007-313	1/4 x 1-1/2	100
5007-316	1/4 x 2	100
5007-444	5/16 x 1	100
5007-448	5/16 x 1-1/2	100
5007-451	5/16 x 2	100
5007-453	5/16 x 2-1/2	100
5007-489	3/8 x 1	100
5007-493	3/8 x 1-1/2	100
5007-496	3/8 x 2	50
5007-498	3/8 x 2-1/2	50
5007-500	3/8 x 3	50
5007-579	1/2 x 1	50
5007-583	1/2 x 1-1/2	50
5007-586	1/2 x 2	50
5007-588	1/2 x 2-1/2	25
5007-590	1/2 x 3	25

For a complete listing of non-ferrous and stainless fasteners see separate Papco Corrosion Resistant Catalogue.