













Project: _____






Fixture Type: _____

Location: _____

Contact/Phone: _____

Trim Series	Dimensions	Aperture	Catalog No.	Housing/Lamp Compatibility
 <p>Tapered Baffle</p>		5 3/4"	24W-WH - White Baffle, White Trim 24B-WH - Black Baffle, White Trim 24B-BL - Black Baffle, Black Trim 24B-ABZ - Black Baffle, Classic Aged Bronze Trim 24B-SC - Black Baffle, Satin Chrome Trim	IC2: 50W PAR30, 75W PAR30L, 65W BR30 TC2/TC2R: 75W PAR30, 75W PAR30L, 65W BR30 IC22 Series: 75W PAR30L, 50W PAR30, 65W BR30 IC22LEDGEN2/IC22SLEDGEN2/IC22RLEDGEN2/TC922LED Series IC22LEDG3/IC22RLEDG3/IC922LEDG3/IC922RLEDG3 Series APT2: 75W PAR30L, 65W BR30 TC922LEDG3 Series, TC1422LED3 Series
 <p>Straight Baffle</p>		5 3/4"	25W-WH - White Baffle, White Trim 25B-WH - Black Baffle, White Trim 25B-BL - Black Baffle, Black Trim 25B-ABZ - Black Baffle, Classic Aged Bronze Trim 25B-SC - Black Baffle, Satin Chrome Trim	IC2: 85W BR40, 90W PAR38 TC2/TC2R: 120W BR40, 150W PAR38 IC22 Series: 50W PAR30, 65W BR30, 65W PAR38 APT2: 150W PAR38, 120W BR40
 <p>Ultra-Trim Baffle - Fully Enclosed</p>		5 7/8"	28W-WH - White Baffle, White Trim 28B-WH - Black Baffle, White Trim	IC2: 75W A19, 100W PAR38, 75W PAR30, 75W PAR30L, 85W BR30, 120W BR40 TC2/TC2R: 150W A21, 150W PAR38, 75W PAR30, 75W PAR30L, 85W BR30, 120W BR40 IC22 Series and IC23 Series: 60W A19, 75W PAR30, 75W PAR30L, 65W BR30, 90W PAR38, 90W BR40 ICPL/PL613: 13W, ICPL/PL618: 18W ICPL626 Series: 26W, ICPL632 Series: 32W, PL642 Series: 42W (For best performance, 26W is recommended) APT2: 150W A21, 150W PAR38, 75W PAR30, 75W PAR30L, 85W BR30, 120W BR40
 <p>Shallow Baffle</p>		5 3/4"	244W-WH - White Baffle, White Trim 244B-WH - Black Baffle, White Trim	IC2/TC2/TC2R: 75W PAR30, 75W PAR30L, 65W BR30 IC21 Series: 50W PAR30, 65W BR30, 75W PAR30L IC22 Series and IC23 Series: 60W PAR30, 65W BR30, 75W PAR30L APT2: 75W PAR30, 75W PAR30L, 65W BR30
 <p>PAR30 Deep Baffle</p>		5 5/8"	254W-WH - White Baffle, White Trim 254B-WH - Black Baffle, White Trim	IC2/TC2/TC2R: 75W PAR30, 100W PAR38
 <p>Economy A-Lamp Reflector with Baffle</p>		5 1/2"	230CW-WH - Clear with White Baffle, White Trim 230CB-WH - Clear with Black Baffle, White Trim	IC2/TC2/TC2R: 100W A19 IC23 Series: 40W A19 APT2: 100W A19

6" TRIM SERIES BAFFLES

Trim Series	Dimensions	Aperture	Catalog No.	Housing/Lamp Compatibility
 A-Lamp Reflector with Black Baffle		5 7/8"	233C-WH - Clear Alzak with Black Baffle, White Trim	IC2: 75W A19 TC2/TC2R: 100W A19, 150W A21 IC23 Series: 40W A19 ICPL/PL613: 13W, ICPL/PL618: 18W, ICPL626 Series: 26W ICPL632 Series: 32W, PL642 Series: 42W APT2: 150W A21
 PAR30 Adjustable Tapered Cone		5 3/4"	264W-WH - White Baffle, White Trim 264B-WH - Black Baffle, White Trim	IC2/TC2/TC2R: 75W PAR30 IC22 Series and IC23 Series: 50W PAR30 APT2: 75W PAR30
			6" trim ring compatible with 24, 25, 244, 254, 264 trims TR6-WH - White TR6-BL - Black TR6-SC - Satin Chrome TR6-ABZ - Classic Aged Bronze	