



TRAC-MASTER®

Tube Trac System

TRAC SECTIONS, MOUNTINGS & JOINERS

TT4 and TT8

Project: _____

Fixture Type: _____

Location: _____

Contact/Phone: _____

PRODUCT DESCRIPTION

Single-circuit trac sections mounted in a 2-1/2" diameter decorative tubular profile for surface or pendant mounting. Compatible with straight, right angle and flexible corner connectors to create straight runs or patterns. Accepts all Trac-Master and Trac-Lites trac fixtures.

PRODUCT SPECIFICATIONS

Construction Extruded aluminum "I" beam channel mounted into 2-1/2" extruded aluminum housing • One-piece thermoplastic insulator • Assembly includes trac section, tubular housing, die-formed end-caps and end-feed/joiner at each end.

Electrical Two 12 gauge solid copper conductors • Rated 20 amps at 120 volts • Aluminum channel used as system ground • One-piece insulator insures consistent conductor spacing for reliable electrical contact • Insulating bushings supplied at mounting hole locations to prevent shorts to ground.



Labels UL listed, CSA certified.

INSTALLATION

Embossed polarity line provides visual cue to proper trac, trac connector and fixture alignment • Integral raceway in top of tube accommodates surface mount bracket, wall outrigger bracket or pendant mounting hardware • Field-cutting to length is not recommended.

Product specifications subject to change without notice.

DIMENSIONS



PRODUCT CODE

Catalog Number	Finish	Description	Actual Length
TT4WH	White	4' One Circuit Trac Tube	48 3/8"
TT4BL	Black	4' One Circuit Trac Tube	48 3/8"
TT8WH	White	8' One Circuit Trac Tube	96 3/8"
TT8BL	Black	8' One Circuit Trac Tube	96 3/8"


TRAC-MASTER®

Tube Trac System


TRAC SECTIONS, MOUNTINGS & JOINERS

TT4 and TT8


Mountings




TT528WH, TT528BL
Surface Mount Bracket. For mounting on T-bar or rigid ceiling. Supports trac housing 1 1/2" from ceiling. Use two for each trac tube section.



TT529WH, TT529BL
Wall Mount Bracket. For mounting trac tube from wall. Trac tube extends 1 1/4" from wall. Use two for each trac tube section.



TT590-12 TT590-36
TT590-18 TT590-48
TT590-24
T-Bar Pendant Stem Kit (12", 18", 24", 36", 48"). Mechanically suspends and electrically feeds trac tube. Feed wires for trac tubes can be routed through stem. Use two for every 4' and 8' Trac Tube. Continuous runs require one every 4'.
WH, BL



TT595WH, TT595BL
T-Bar ceiling Pendant cable. Mechanical only suspension for trac tubes. Adjustable 48" flexible cable. Continuous runs require one cable every 4'.

TT596WH, TT596BL
T-Bar ceiling Pendant cable with electrical feed. Similar to above but with 48" electrical feed flexible wireways and wires.

TT597WH, TT597BL
Rigid ceiling Pendant cable. Mechanical only suspension for tubes. Adjustable 48" flexible cable. Continuous runs require one cable every 4'.

TT598WH, TT598BL
Rigid ceiling Pendant cable with electrical feed. Similar to above but with 48" electrical feed flexible wireways and wires.




T96WH, T96BL
Pendant Stem Threaded Coupling. Enables multiple pendant stems to be joined for higher ceiling applications.




T94WH, T94BL
Sloped Ceiling Adapter. Allows **TT590** or **TT591** pendant to hang straight down from sloped ceilings. Can be used to feed electrical wires to Trac at up to 60° angle.


Joiner Kits



TT503WH, TT503BL
Straight Joiner Kit. Joins two trac tube sections in a straight run. Includes electrical jumpers, joiner bracket and joiner cover.



TT520WH, TT520BL
Flexible Accordion Joiner. Joins two trac tube sections. Adjusts from 60° to 300°. Includes electrical jumpers and joiner brackets.



TT524WH, TT524BL
90° Right Angle Corner. Joins two trac tube sections. Includes electrical jumpers and joiner brackets.

Product specifications subject to change without notice.



1300 S. Wolf Road • Des Plaines, IL 60018 • Phone (847) 827-9880 • Fax (847) 827-2925
220 Chrysler Drive • Brampton, Ontario • Canada L6S 6B6 • Phone (905) 792-7335 • Fax (905) 792-0064
Visit us at www.junolightinggroup.com

Printed in U.S.A. ©2009 Juno Lighting, LLC.