



Markers that withstand oil, water and humidity!

Vinyl Cloth, Standard Books

- Choose the numbers or letters you need
- Wide selection of sizes and legends
- Size 3" x 5" (76 mm x 146 mm)
- Material: vinyl cloth
- Cover keeps markers clean
- Books are 3" x 5½" pocket size
- 10 pages per book



Pocket pack wire marker books are easy to carry, and easy to use. The material is an all-purpose vinyl coated cloth tape exclusively designed to resist abrasion, oil, water, and dirt.

From Thomas & Betts you get the one-piece wire marker and terminal marker. A slight die-cut enables you to easily remove the terminal marker if you need it or leave it in place for a longer marker.



EZCODE®

CAT. NO.	NUMBER OF MARKERS AND LEGENDS
WM-0 THRU 9	40 Markers each: 0 thru 9; 10 Markers each: T1, T2, T3, L1, L2, L3
WM-0-9M	46 Markers each page; full page of 1, full page of 2, etc.
WM-0-45	10 Markers each: 0 thru 45
WM-46-90	10 Markers each: 46 thru 90
WM-A-Z	10 Markers each: A thru Z, +, -, and 0 thru 15
WM-123	150 Markers each: 1, 2, 3
WM-ABC	150 Markers each: A, B, C
WM-A-33	10 Markers each: 1 thru 33, A, B, C, +, -, T1, T2, T3, L1, L2, L3
WM-A-90	6 Markers each: 0 thru 15; 4 Markers each: 1
WM-0 THRU WM-9	6 thru 90: 2 Markers each; A thru Z 460 Markers each of any number 0 thru 9
WM-A, -B, -C, -D, -E, -F, -G, -L, -N, -P, -R, -S, -T, OR X	460 Markers each of any letter: -A, -B, -C, -D, -E, -F, -G, -L, -N, -P, -R, -S, -T or X
WM-GRD	120 Markers: ⅞" x 2½" or 240 Markers ⅞" x 1¼" with "GRD" legend
WMLC-1	24 Legends, 2 legends each per page, 480 Markers per book for house wiring and circuit breakers; ⅝" x 1½" (16mm x 10mm)

Order multiple 10 books

CAT. NO.	NUMBER OF MARKERS AND LEGENDS
WM-T3	10 Pages T ₁ , T ₂ , T ₃ ; 140 Markers ea.; total 420
WM-L3	10 Pages L ₁ , L ₂ , L ₃ ; 140 Markers ea.; total 420
WM-9T	3 Pages 1, 2, 3; 42 Markers ea.; 3 Pages A, B, C; 42 Markers ea.; 2 Pages T ₁ , T ₂ , T ₃ ; 28 Markers ea.; 2 Pages L ₁ , L ₂ , L ₃ ; 28 Markers ea.; total 140
WM-1-30	10 Pages 1-30; 14 Markers ea.; total 140
WM-12	A-Z 8½ Pages, 14 Markers ea.; Blank Write Ons 1 Page, 22 Markers ea.; Plus & Minus ⅓ Page, 7 Markers ea.; total 393
WM-13	Plus & Minus, AC, DC, 1 Page ea., 46 Markers ea.; Pos. Neg. Gnd. 1 Page ea., 28 Markers ea.; Spare, Neut. 1 Page ea., 22 Markers ea.; Blank Write-Ons 1 Page ea., 22 Markers ea.; total 256
WM-0-90	5 Pages ea. 0-45; 5 Markers ea.; 5 Pages ea. 46-90; 5 Markers ea.; total 455