NetKey[™] Surface Mount Boxes



Surface mount boxes shall have a low profile design and shall be available in a variety of port densities. Boxes shall accept all NetKey[™] Keystone Modules for fiber, copper, and audio/video applications. The boxes shall mount with screws, adhesive, or optional magnets and shall include breakouts for use with surface raceway. Cable tie slots shall be included to provide strain relief on incoming cables.





NetKey [™] Surface Mount Boxes*				
2-port: 4-port: 6-port:	NK2BXIW-A NK4BXIW-AY NK6BXIW-AY			
Accessories				
Screw cover:	CSC*-X			
Label/label cover kit:	CSGLLC-L			
Magnet:	CBM-X			

technical information

Mounting options:	Mounts easily with screws, adhesive tape, or optional magnet
Material:	Box is made of ABS

key features and benefits

Modular	Accepts all NetKey [™] Keystone Modules which snap in and out for easy moves, adds, and changes		
Low profile design	Presents a more discreet or inconspicuous look		
Raceway breakouts	Compatible with specific surface raceway, conceals cable entering the box		
Cover screw	Select boxes provide a screw that secures the cover to the base		
Labels and label covers	Select boxes include a label pocket to meet TIA/EIA-606B labeling standards		
Magnet pockets	Accept magnets for mounting on metal surfaces; NK2BX*-A, NK4BX*-AY		

Part Number	Compatible Raceway	No. of Adhesive Strips	No. of Cable Ties	Label/Label Cover Included	Mounting Screws Included	Magnet Pockets
NK2BX	LD3, LDP3, LD5, LDP5	1	1	No	Yes	1
NK4BX	LD3, LDP3, LD5, LDP5, LD10, LDP10	2	2	Yes	Yes	2
NK6BX	LD3, LDP3, LD5, LDP5, LD10, LDP10	2	2	Yes	Yes	None


applications


NetKey[™] Surface Mount Boxes offer a variety of mounting options, allowing NetKey[™] Keystone Modules to be mounted on a variety of surfaces, such as standard walls, metal surfaces, office furniture, etc. Surface mount


boxes include breakouts compatible with Panduit's Surface Raceway system to conceal and allow cable to run into the box providing a point of connection for voice, video, and data applications. *For standard colors other than IW (Off White), replace suffix with EI (Electric Ivory), WH (White), IG (International Gray), or BL (Black).

NetKey[™] Surface Mount Boxes


2-Port Surface Mount Box NK2BXIW-A








4-Port Surface Mount Box NK4BXIW-AY



6-Port Surface Mount Box NK6BXIW-AY



Dimensions are in inches. [Dimensions in brackets are metric].

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA Markham, Ontario cs-cdn@panduit.com Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK cs-emea@panduit.com Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore cs-ap@panduit.com Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan cs-japan@panduit.com Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico cs-la@panduit.com Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia cs-aus@panduit.com Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty



For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300 and reference ©2014 Panduit Corp. ALL RIGHTS RESERVED NKDS45--WW-ENG 3/2014