Mini-Com® Surface Mount Boxes



Surface Mount Boxes shall have a low profile design and be available in a variety of port densities. Boxes shall accept most Mini-Com® Modules for fiber, copper, and audio/video applications. The boxes shall mount with screws, adhesive, or optional magnets. The box covers include breakouts for use with surface raceway. Cable tie slots shall be included to provide strain relief on incoming cables. Select boxes shall include a cover with a quick release feature.



technical information

Mounting option:	Mounts easily with screws, adhesive tape or optional magnet			
Material:	Box is made of ABS			
UL rated:	UL 1863; UL 2043 for 1 and 2 position boxes			

Compatible raceway, magnets, and packaging:

Part Number	Breakout Suitable for:	No. of Adhesive Strips	No. of Cable Ties	Label/ Label Cover Included	Mounting Screws Included	Screw Cover Included	Magnet Pockets
CBXQ1**-A	LD3/LDPH3	1	1	No	No	No	1
CBXQ2**-A	LD3/LDPH3 LD5/LDPH5	2	1	Yes	No	Yes	1
CBXQ4**-A	LD3/LDPH3 LD5/LDPH5 LD10/LDPH10	2	2	Yes	No	Yes	2
CBXQ6**-A	LD3/LDPH3 LD5/LDPH5 LD10/LDPH10	2	2	Yes	No	Yes	2
CBX1**-A*	LD3/LDPH3	1	0	No	No	No	0
CBX2**-A	LD3/LDPH3 LD5/LDPH5	1	1	No	Yes	No	1
CBX4**-A	LD3/LDPH3 LD5/LDPH5	2	2	Yes	Yes	Yes	2

^{*}Raceway does not enter box.

key features and benefits

Quick release cover	Can be removed by hand, does not require tool			
Modular	Accepts most Mini-Com® Modules, for easy moves, adds, and changes			
Low profile design	Smaller profile offers a less conspicuous look			
Raceway breakouts	Compatible with specific raceway, conceals cable entering the box			
Cover screw	Boxes with label pocket provide a screw that secures the cover to the base			
Labels and label covers	Select boxes include a label pocket to meet TIA/EIA-606B labeling standards			
Magnet pockets	Magnet can be used with magnet pocket for optional mounting (CBX1**-A does not include a magnet pocket); CBM-X for use with standard boxes			
Shuttered feature	Achieved by installing jack modules with spring shuttered door			
UL 2043	1 and 2 pos are suitable for installations in air handling spaces			

applications

Mini-Com® Surface Mount Boxes offer a variety of mounting options, allowing Mini-Com® Modules to be mounted on a variety of surfaces, such as standard walls, metal surfaces, office furniture, etc.

Surface mount boxes include breakouts compatible with Panduit's raceway system to conceal and allow cable to run into the box providing a point of connection for voice, video and data applications.

Mini Com® Blanks can be used to reserve space for future expansion.

Quick cover removal provides easy access for moves, adds and changes with the ability to secure cover to base if needed.

1 and 2 position comply with UL 2043 making them suitable for air handling spaces.



Mini-Com[®] Surface Mount Boxes with Quick Release Cover

 1-port:
 CBXQ1**-A^

 2-port:
 CBXQ2**-A^

 4-port:
 CBXQ4**-A^

 6-port:
 CBXQ6**-A^

Elongated Surface Mount Boxes:

One

module space: CBX1**-A^

Two

module space: CBX2**-A^

Four

module space: CBX4**-A

Accessories:

Blank module: CMB**-X

Magnet

(quick release boxes): CQBM-X (elongated boxes): CBM-X


Category 5e, 6 and 6A couplers are not compatible with surface mount boxes.

**To designate color, add suffix EI (Electric Ivory), IW (Off White), IG (International Gray), WH (White), BL (Black), AW (Arctic White).


[^]Suitable for air handling spaces


Mini-Com® Surface Mount Boxes


Mini-Com® Surface Mount Boxes with Quick Release Cover



Mini-Com® Surface Mount Boxes







Dimensions are in inches. [Dimensions in brackets are metric].

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA Markham, Ontario cs-cdn@panduit.com Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK cs-emea@panduit.com Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore cs-ap@panduit.com Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan cs-japan@panduit.com Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico cs-la@panduit.com Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia cs-aus@panduit.com Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty



Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300



