

Contact/Phone:

TRAC-MASTER®

Project:

Fixture Type:

Location:

Avant Garde

FRONT LAMPING OPEN BACK SPOTLIGHTS

T687, T689 and T690

PRODUCT DESCRIPTION

The clean, functional lines of the open back allows maximum adjustability. Front Loading Open Back Spotlights relamp from the front and have fixed socket mount and on/off switch. The minimum profile with stylized yoke design is ideal for retail and commercial applications.

Construction Die formed steel.

Socket Medium base porcelain with nickel plated copper screw shell.

Aiming 90° vertical aiming capability and 358° rotation.

Juno Universal Trac Adapter Compatible with Juno Trac-Master 1 or 2-circuit systems or Juno Trac-Lites system • Copper alloy contacts provide precise spring action - no arcing and will not take a set • True, positive electrical ground • On/off switch included • Patented embossed polarity arrows on bottom of adapter • Spring-loaded positive latch with embossed polarity arrows secures trac light to trac • "Pull-up" contact to up position for two-circuit application.

Alternate TEK Trac Adapter Compatible with Juno TEK trac system • System specific and assembled to trac fixture • Integrally polarized construction to prevent reverse installation – only allows insertion in proper orientation • Rotary circuit selector enables simple switching between circuits • Integral on/off switch enables individual fixtures to be switched for servicing.

Labels UL listed, CSA certified.

Specifications subject to change without notice.




Line Voltage PAR20

Catalog Number	Description	Finish	Lamp
T687 WH	Open Back w/Universal Trac Adapter	White	50W PAR20
T687 BL	Open Back w/Universal Trac Adapter	Black	50W PAR20
T687 SL	Open Back w/Universal Trac Adapter	Silver	50W PAR20
T687 NAT	Open Back w/Universal Trac Adapter	Natural	50W PAR20
T687 TEK WH	Open Back w/TEK Trac Adapter	White	50W PAR20
T687 TEK BL	Open Back w/TEK Trac Adapter	Black	50W PAR20
T687 TEK SL	Open Back w/TEK Trac Adapter	Silver	50W PAR20
T687 TEK NAT	Open Back w/TEK Trac Adapter	Natural	50W PAR20



Line Voltage PAR30

Catalog Number	Description	Finish	Lamp
T689 WH	Open Back w/Universal Trac Adapter	White	75W PAR30
T689 BL	Open Back w/Universal Trac Adapter	Black	75W PAR30
T689 SL	Open Back w/Universal Trac Adapter	Silver	75W PAR30
T689 NAT	Open Back w/Universal Trac Adapter	Natural	75W PAR30
T689 TEK WH	Open Back w/TEK Trac Adapter	White	75W PAR30
T689 TEK BL	Open Back w/TEK Trac Adapter	Black	75W PAR30
T689 TEK SL	Open Back w/TEK Trac Adapter	Silver	75W PAR30
T689 TEK NAT	Open Back w/TEK Trac Adapter	Natural	75W PAR30



Line Voltage PAR38

Catalog Number	Description	Finish	Lamp
T690 WH	Open Back w/Universal Trac Adapter	White	250W PAR38
T690 BL	Open Back w/Universal Trac Adapter	Black	250W PAR38
T690 SL	Open Back w/Universal Trac Adapter	Silver	250W PAR38
T690 NAT	Open Back w/Universal Trac Adapter	Natural	250W PAR38
T690 TEK WH	Open Back w/TEK Trac Adapter	White	250W PAR38
T690 TEK BL	Open Back w/TEK Trac Adapter	Black	250W PAR38
T690 TEK SL	Open Back w/TEK Trac Adapter	Silver	250W PAR38
T690 TEK NAT	Open Back w/TEK Trac Adapter	Natural	250W PAR38

