


# 2 1/2" Bungalow Service



## ENTRANCE STACKS & ACCESSORIES

MAST AND ACCESSORIES

CATALOGUE #	DESCRIPTION
<b>2521</b> <b>2521-1-1/2</b> <b>2521-2</b>	100 Amp entrance cap - completely weatherproof As 2521 but with insert for 200 Amp or 150 Amp service 2" Cap for 200 Amp service
<b>2508</b> <b>2509</b> <b>2510</b> <b>2512</b>	Service Entrance Masts - 2 1/2" O.D. 8 Ft. Service Entrance Mast 9 Ft. Service Entrance Mast 10 Ft. Service Entrance Mast 12 Ft. Service Entrance Mast
<b>25C</b> <b>2515</b> <b>2517-U</b> <b>2518-U</b> <b>417U</b> <b>2513</b>	Service mast ground clamp Guy attachment with eye bolt 200 Amp heavy duty triplex cable rack 100 Amp light duty triplex cable rack Oversize Cable Rack for 3" Pipe Guy attachment with hook
<b>2506B</b>  <b>2506</b> <b>2506NB</b> <b>2506N-2</b> <b>2526NB</b> <b>2526N</b> <b>2506-3</b>	Weatherproof Roof Flange c/w Steel Collar (No longer available - Substitute 2526NB) Complete with undereave flashing All neoprene roof flange - one piece construction Neoprene Collar only Steel roof flange with neoprene collar - 2 piece construction As 2526NB but c/w undereave flashing Undereave flashing only
<b>2014-U</b> <b>2504</b>  <b>2505</b> <b>2504-6</b> <b>2504-12</b> <b>2504-LB</b>	Clamp - 1/2" diameter Clamp assembly for mounting stack on brick, concrete block, etc. Complete with 4" x 4" galvanized washer and 5/8" x 10" bolt As above with 5/8" x 4 1/2" bolt std. thread for wood frame As above with 5/8" x 6" bolt std. thread As above with 5/8" x 12" bolt As above less thru bolt & washer
<b>2507-5/8</b>  <b>506-5/8</b> <b>506</b> <b>5061</b> <b>2516</b> <b>2516-L</b>	Meter spacer c/w pipe strap. c/w 5/8" x 4 1/2" Carrige bolt and 4" x 4" Washer As above less stack clamp Meter spacer only (Z plate) Meter spacer (top hat) Stack clamp for surface mounting Same as above but c/w 3 lag screws 3/8" x 3"
<b>2501</b> <b>2525</b> <b>2550</b> <b>2502</b> <b>2502MS</b>	Add "M" to catalogue # (eg. 2501-M) for male thread. 1" Bottom Reducer 1 1/4" Bottom Reducer 1 1/2" Bottom Reducer 2" Bottom Reducer 2" Reducer Offset (Special)

