

4 in. Square boxes

Tile ring covers



BC52C49-1/2 to CI52-C-51-2



52 C 52 1/2 to 52 C 54 2



52CADJ



Cat. No.	Description
One device square cornered tile covers	
BC52C49-1/2	Raised 1/2 in. (3.4 cu. in.)
BC52C49-3/4	Raised 3/4 in. (5.3 cu. in.)
BC52-C-49-5/8	Raised 5/8 in. (4.3 cu. in.)
BC52-C-49-1	Raised 1 in. (6.8 cu. in.)
CI52-C-49-1 1/4	Raised 1 1/4 in. (8.6 cu. in.)
CI52-C-50-1 1/2	Raised 1 1/2 in. (10.0 cu. in.)
CI52-C-51-2	Raised 2 in. (14.0 cu. in.)
One device square cornered tile covers - adjustable	
52CADJ	Adjustable from 1/2 in. to 1 1/2 in. raise (from 3.4 to 10.0 cu. in.)
Two device square cornered tile covers	
52 C 52 1/2	Raised 1/2 in. (6.0 cu. in.)
52 C 52 5/8	Raised 5/8 in. (8.3 cu. in.)
52 C 52 3/4	Raised 3/4 in. (9.0 cu. in.)
52 C 52 1	Raised 1 in. (12.5 cu. in.)
52 C 52 1 1/4	Raised 1 1/4 in. (15.5 cu. in.)
52 C 53 1 1/2	Raised 1 1/2 in. (19.0 cu. in.)
52 C 54 2	Raised 2 in. (25.5 cu. in.)

4 in. Square boxes

Covers



BC8361



BC8362



BC8363



BC8364



BC8365



BC8366



BC8367



Cat. No.	Description
3/8 in. raised surface covers (4.6 cu. in.) device mount	
BC8361	One toggle switch
BC8362	For 2 5/8 in. diameter 30 / 50 A single receptacle
BC8363	For 1 13/32 in. diameter 15 A single receptacle
BC8364	For 1 19/32 in. diameter 20 / 30 A single locking receptacle
BC8365	One duplex receptacle
BC8366	For 2 9/64 in. diameter 30 A single receptacle
BC8367	Two toggle switches

Complete with device mounting screws

Cover	NEMA Configuration							
	A	V	Pole	Wire	Phase	Rec. Dia	NEMA	
BC8363	15	125	2	3	1	1.406	5-15R	
BC8364	20	125	2	3	1	1.562	L5-20R	
BC8364	20	250	2	3	1	1.562	L6-20-R	
BC8364	20	347	2	3	1	1.562	L24-20R	
BC8364	20	600	2	3	1	1.562	L9-20R	
BC8364	20	125/250	3	3	1	1.562	L10-20R	
BC8364	20	250	3	3	3	1.562	L11-20R	
BC8364	20	125/250	3	4	3	1.562	L14-20R	
BC8366	30	125	2	3	1	2.109	5-30R	
BC8364	30	125	2	3	1	1.562	L5-30R	
BC8366	30	250	2	3	1	2.109	6-30R	
BC8364	30	250	2	3	1	1.562	L6-30R	
BC8362	30	125/250	3	4	3	2.647	14-30R	
BC8362	50	125/250	3	4	1	2.647	14-50R	

4 in. Square boxes

Covers



BC8368



BC8371



BC8375



BC8376



BC8377



BC8378



BC97002



Cat. No.	Description
³/₈ in. raised surface covers (4.6 cu. in.)	
BC8368	2 Decora/GFCI
BC8371	Two duplex receptacles
BC8375	One toggle switch, one duplex receptacle
BC8376	One Decora/GFCI
BC8377	One toggle switch, one Decora/GFCI
BC8378	One duplex receptacle, one Decora/GFCI
GFCI Conversion kits (stainless steel / steel)	
BC97002	To install GFCI on 4 in. square boxes. Complete with mounting screws

Complete with device mounting screws.

When extra capacity is required, the 8300 Series of 4 in. square covers can be mounted on a 72 Series of 4 11/16 in. square boxes using a C172-A-52 adaptor. (see page A46)