




















# 4" LOW VOLTAGE TRIM SERIES DECORATIVE

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact/Phone: \_\_\_\_\_

Trim Series	Dimensions	Aperture	Catalog No.	Housing/Lamp Compatibility
 <b>Beveled Lensed</b>			<b>4402-ABZ</b> - Regressed Perimeter Frosted Glass Lens, Classic Aged Bronze Trim <b>4402-SC</b> - Regressed Perimeter Frosted Glass Lens, Satin Chrome Trim <b>4402-WH</b> - Regressed Perimeter Frosted Glass Lens, White Trim	IC44N/IC44W/IC44S/TC44/TC44V/TC44S/TC44R: 50W MR16
 <b>Beveled Dome Lensed</b>			<b>4401-ABZ</b> - Frosted Glass Lens, Classic Aged Bronze Trim <b>4401-SC</b> - Frosted Glass Lens, Satin Chrome Trim <b>4401-WH</b> - Frosted Glass Lens, White Trim	IC44N/IC44W/IC44S/TC44/TC44V/TC44S/TC44R: 50W MR16
 <b>Beveled Cone</b>	 Adjustment: 30° Vertical	3 3/8"	<b>4404HZ-SC</b> - Haze, Satin Chrome Trim <b>4404WHZ-ABZ</b> - Wheat Haze, Classic Aged Bronze Trim	IC44N/IC44W/IC44S/TC44/TC44V/TC44S/TC44R: 50W MR16
 <b>Beveled Cylinder</b>	 Adjustment: 30° Vertical	3"	<b>4403FROST-SC</b> - Frost Glass, Satin Chrome Trim <b>4403FROST-WH</b> - Frost Glass, White Trim	IC44N/IC44W/IC44S/TC44/TC44V/TC44S/TC44R: 50W MR16
 <b>Glass Cylinder</b>		2 5/8"	<b>4450MESH-SC</b> - Mesh Glass, Satin Chrome Trim	IC44N/IC44W/IC44S/TC44/TC44V/TC44S/TC44R: 50W MR16
 <b>Frosted Glass</b>			<b>4481CLEAR</b> - Perimeter Frosted Clear Glass	IC44N/IC44W/IC44S/TC44/TC44V/TC44S/TC44R: 50W MR16
 <b>Solid Glass Collar</b>		2 5/8"	<b>4480FROST</b> - Frost Glass	IC44N/IC44W/IC44S/TC44/TC44V/TC44S/TC44R: 50W MR16



1300 S. Wolf Road • Des Plaines, IL 60018 • Phone (847) 827-9880 • Fax (847) 827-2925  
220 Chrysler Drive • Brampton, Ontario • Canada L6S 6B6 • Phone (905) 792-7335 • Fax (905) 792-0064  
Visit us at [www.junolightinggroup.com](http://www.junolightinggroup.com)

Printed in U.S.A. ©2010 Juno Lighting, LLC.