

## PLATED GRADE 5 HEX HEAD CAP SCREWS BOULONS HEX CLASSE 5 PLAQUÉS

**075**  
UNC  
Coarse

**076**  
UNF  
Fine

- Made to S.A.E. J429 specifications.
- Medium carbon Steel.
- Double heat treated.
- Bright Electroplated with Chromate Finish.



Papco® Plated Grade 5 Cap Screws are identified by the three radial bar head marking and are made of medium carbon steel, quenched and tempered for higher Tensile strength and holding power. Bright Electroplated with Chromate finish to resist rust. Tensile strength: up to 1" Dia.-120,000 p.s.i. (min.) 1-1/8" Dia. up-105,000 p.s.i. (min.)

### ORDER BY STOCK NUMBER

Example of Stock No. 075-586 is 1/2 x 2 Coarse Thread Plated Grade 5 Cap Screw.

UNC Coarse Thread Plated, add prefix 075

UNF Fine Thread Plated, add prefix 076

Threads per inch	UNC	20	18	16	14	13	12	11	10	9	8	7
	UNF	28	24	24	20	20	18	18	16	14	14	12
Diameter	1/4	5/16	3/8	7/16	1/2	9/16	5/8	3/4	7/8	1	1-1/4	
1/2	-305	-440	-	-	-	-	-	-	-	-	-	-
3/4	-307	-442	-487	-532	-	-	-	-	-	-	-	-
1	-309	-444	-489	-534	-579	-623	-668	-	-	-	-	-
1-1/4	-311	-446	-491	-536	-581	-625	-670	-	-	-	-	-
1-1/2	-313	-448	-493	-538	-583	-627	-672	-714	-	-	-	-
1-3/4	-315	-450	-495	-540	-585	-	-674	-716	-761	-802	-	-
2	-316	-451	-496	-541	-586	-630	-675	-717	-762	-803	-	-
2-1/4	-317	-452	-497	-	-587	-	-676	-718	-763	-804	-	-
2-1/2	-318	-453	-498	-543	-588	-632	-677	-719	-764	-805	-885	-
3	-320	-455	-500	-545	-590	-634	-679	-721	-766	-807	-887	-
3-1/2	-322	-457	-502	-547	-592	-	-681	-723	-768	-809*	-889	-
4	-324	-459	-504	-549	-594	-	-683	-725	-770	-811*	-891	-
4-1/2	-325	-460	-505	-	-595	-	-684	-726	-771	-812*	-892	-
5	-326	-461	-506*	-	-596	-	-685	-727	-772	-813*	-893	-
5-1/2	-	-	-	-	-597	-	-686	-728	-773*	-814*	-894	-
6	-	-	-509*	-554	-599*	-	-688	-730	-775*	-816*	-896	-
Head Width Across Flats	7/16	1/2	9/16	5/8	3/4	13/16	15/16	1-1/8	1-5/16	1-1/2	1-7/8	
Head Height	5/32	13/64	15/64	9/32	5/16	23/64	25/64	15/32	35/64	39/64	25/32	
Standard Package	100	100	100 50*	50	20 25*	25	25	20	20 10*	20 10*	As Required	

## PLATED GRADE 5 HEX NUTS ÉCROUS HEX CLASSE 5 PLAQUÉS

**087**  
UNC  
Coarse

**088**  
UNF  
Fine

- Made to Standard Finished Hexagon Nut dimensions.
- Bright Electroplated with Chromate Finish.



Stock No.	Diameter	1/4	5/16	3/8	7/16	1/2	9/16	5/8	3/4	7/8	1
		UNC Coarse	087-014	087-016	087-018	087-020	087-022	087-023	087-024	087-026	087-028
	UNF Fine	088-014	088-016	088-018	088-020	088-022	088-023	088-024	088-026	088-028	088-030
	Standard Package	100	100	100	50	50	25	25	20	20	20

## PLATED BULK FASTENERS ATTACHES EN VRAC PLAQUÉS

- 1/8 keg - 25 lbs. (maximum).
- Bright Electroplated with chromate finish.

Papco® Plated Grade 5 Cap Screws, Hex Nuts, Washers, Carriage Bolts, Lag Bolts and Screw Products series No. 845.

Refer to the current jobber or dealer price books for bulk quantities and sizes.

